

LOW VOLTAGE

SFE Fast-Acting Type



ELECTRICAL CHARACTERISTICS:

% of Ampere Rating	Opening Time
110%	4 hours, Minimum
135%	1 hour, Maximum
200%	10 seconds, Maximum

APPROVALS: Listed by Underwriters Laboratories.


DESIGN STANDARDS: U.L. Standard 275. SAE (Society of Automotive Engineers) J554.

ORDERING INFORMATION:

Catalog Number	Ampere Rating	Voltage Rating	Fuse Length
307 004	4	32	5/8"
307 006	6	32	3/4"
307 07.5	7 1/2	32	7/8"
307 009	9	32	7/8"
307 014	14	32	1 1/16"
307 020	20	32	1 1/4"
307 030	30	32	1 3/16"



3AG Fast-Acting Type



ELECTRICAL CHARACTERISTICS:

% of Ampere Rating	Ampere Rating	Opening Time
100%	4-35	4 hours, Minimum
135%	4-35	1 hour, Maximum
200%	4-30	10 seconds, Maximum
200%	35	20 seconds, Maximum

APPROVALS: Listed by Underwriters Laboratories and Certified by CSA through 30 amperes.

DESIGN STANDARDS: U.L. Standard 275.

ORDERING INFORMATION:

Catalog Number	Ampere Rating	Voltage Rating
311 004	4	32
311 005	5	32
311 006	6	32
311 007	7	32
311 07.5	7 1/2	32
311 008	8	32
311 010	10	32
311 012	12	32
311 015	15	32
311 025	25	32
311 030	30	32
311 035	35	32

For 20-ampere rating use 307 020.

