




30X30X10mm




General Specifications

Airflow	2.5~4.0 CFM
Static Pressure	2.0~5.2 mm-H2O
Housing	Plastic Material UL 94V-0 P.B.T.
Blade	Plastic Material UL 94V-0 P.B.T.
Lead Wire	UL1571 #28 AWG

Dimensions:mm



Performace



Specifications

Model NO.	Bearing	Rated Voltage VDC	Operating Voltage Range VDC	Speed RPM	Airflow CFM	Static Pressure mm-H2O	Current mA	Power W	Life at 40°C L10 HOUR	P-Q Curve	Noise dBA	Weight g
GD053010LB-N	2BALL	5	4~5.5	5800	2.5	2.0	50	0.25	80000	4	<17	9
GD053010MB-N	2BALL	5	4~5.5	6800	3.0	2.7	80	0.40	80000	3	18.0	9
GD053010HB-N	2BALL	5	4~5.5	7800	3.4	3.3	90	0.45	75000	2	21.5	9
GD053010EB-N	2BALL	5	4~5.5	10000	4.0	5.2	120	0.60	65000	1	28.0	9
GD053010LL-N	Sintetico	5	4~5.5	6000	2.6	2.0	80	0.40	50000	4	<17	9
GD053010ML-N	Sintetico	5	4~5.5	7000	2.9	2.8	105	0.53	50000	3	20.5	9
GD053010HL-N	Sintetico	5	4~5.5	8000	3.3	3.6	130	0.65	50000	2	23.2	9
GD053010EL-N	Sintetico	5	4~5.5	10000	4.0	5.2	190	0.95	50000	1	28.0	9
GD123010LB-N	2BALL	12	9~13.2	5800	2.5	2.0	35	0.42	80000	4	<17	9
GD123010MB-N	2BALL	12	7~13.2	6800	3.0	2.7	40	0.48	80000	3	18.0	9
GD123010HB-N	2BALL	12	7~13.2	7800	3.4	3.3	40	0.48	75000	2	21.5	9
GD123010EB-N	2BALL	12	7~13.2	10000	4.0	5.2	60	0.72	65000	1	28.0	9
GD123010LL-N	Sintetico	12	9~13.2	6000	2.5	2.0	35	0.42	50000	4	<17	9
GD123010ML-N	Sintetico	12	7~13.2	7000	2.9	2.8	50	0.60	50000	3	20.5	9
GD123010HL-N	Sintetico	12	7~13.2	8000	3.3	3.6	60	0.72	50000	2	23.2	9
GD123010EL-N	Sintetico	12	7~13.2	10000	4.0	5.2	80	0.96	50000	1	28.0	9