

ADDA USA
DC FAN SPECIFICATIONS

| Frame Dimensions (mm) | Model Part Number | Bearing Type | Volts (V) | Current (A) | Power (W) | Speed (RPM) | Air Flow (CFM) | Pressure (Inches) | Noise (dB/A) | Weight (g) | Features Available | Safety Approvals | Units Per Box | Box Wt. (lbs.) |
|-----------------------|-------------------|--------------|-----------|-------------|-----------|-------------|----------------|-------------------|--------------|------------|--------------------|-------------------|---------------|----------------|
| 60 X 60 X 25 | AD0612HX-A70GL | HYPRO | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 0,1,2 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HX-A73GL | HYPRO | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 3,6 | UL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UX-A70GL | HYPRO | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 0 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UX-A71GL | HYPRO | 12 | 0.27 | 3.24 | 5300 | 28.3 | 0.250 | 37.0 | 68 | 1 | UL,CUL,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UX-A72GL | HYPRO | 12 | 0.27 | 3.24 | 5300 | 28.3 | 0.250 | 37.0 | 68 | 2,3 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612LB-A70GL | BALL | 12 | 0.08 | 0.96 | 2500 | 13.2 | 0.063 | 16.1 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612LB-A70(T) | BALL | 12 | 0.08 | 0.96 | 2300 | 10.7 | 0.041 | 14.5 | 68 | 0,6 | UL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MB-A70GL | BALL | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 0 | UL,CUL,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MB-A71GL | BALL | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MB-A72GL | BALL | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 2,3 | UL,CUL,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MB-A76GL | BALL | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HB-A70GL | BALL | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HB-A72GL | BALL | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 2,3,6 | UL,CUL,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UB-A70GL | BALL | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 0 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UB-A71GL | BALL | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 1 | UL,CUL,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UB-A72GL | BALL | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 2,3 | UL,CUL,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612UB-A76GL | BALL | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612XB-A71GL | BALL | 12 | 0.38 | 4.56 | 6100 | 31.4 | 0.320 | 42.9 | 68 | 1,2,3 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612XB-A72/UP | BALL | 12 | 0.65 | 7.80 | 7400 | 38.1 | 0.500 | 47.8 | 68 | 2 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612LS-A70GL | S | 12 | 0.08 | 0.96 | 2500 | 13.2 | 0.063 | 16.1 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612LS-A73GL | S | 12 | 0.08 | 0.96 | 2500 | 13.2 | 0.063 | 16.1 | 68 | 3 | UL,CUL,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612LS-A76GL | S | 12 | 0.08 | 0.96 | 2500 | 13.2 | 0.063 | 16.1 | 68 | 6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MS-A70GL | S | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 0 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612MS-A76GL | S | 12 | 0.14 | 1.68 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 6 | TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HS-A70GL | S | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HS-A72GL | S | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 2,6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612HS-A73GL | S | 12 | 0.23 | 2.76 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 3 | UL,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612US-A70GL | S | 12 | 0.25 | 3.00 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 0,6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612US-A71GL | S | 12 | 0.27 | 3.24 | 5300 | 28.3 | 0.250 | 37.0 | 68 | 1 | TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0612US-A73GL | S | 12 | 0.27 | 3.24 | 5300 | 28.3 | 0.250 | 37.0 | 68 | 3 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624MX-A70GL | HYPRO | 24 | 0.08 | 1.92 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 0 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624MX-A76GL | HYPRO | 24 | 0.08 | 1.92 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HX-A70GL | HYPRO | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HX-A72GL | HYPRO | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 2 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624UX-A71GL | HYPRO | 24 | 0.16 | 3.84 | 5000 | 28.3 | 0.250 | 37.0 | 68 | 1,2 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624LB-A70GL | BALL | 24 | 0.05 | 1.20 | 2500 | 16.0 | 0.079 | 16.1 | 68 | 0 | UL,CUL,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624MB-A70GL | BALL | 24 | 0.08 | 1.92 | 3500 | 18.0 | 0.118 | 24.0 | 68 | 0,1 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HB-A70GL | BALL | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 0 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HB-A71GL | BALL | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 1 | UL,CSA,TUV,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HB-A72GL | BALL | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 2,3 | UL,CUL,CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624HB-A76GL | BALL | 24 | 0.15 | 3.60 | 4500 | 23.2 | 0.188 | 32.3 | 68 | 6 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624UB-A70GL | BALL | 24 | 0.16 | 3.84 | 5000 | 26.5 | 0.204 | 38.1 | 68 | 0,1,2,3 | CE | 300 | 44.00 |
| 60 X 60 X 25 | AD0624LS-A70GL | S | 24 | 0.05 | 1.20 | 2500 | 16.0 | 0.079 | 16.1 | 68 | 0 | UL,CUL,TUV,CSA,CE | 300 | 44.00 |

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED