

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
92 X 92 X 25	AD0912UX-A76GL	HYPRO	12	0.30	3.60	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912DB-A71GL	BALL	12	0.07	0.84	1600	28.0	0.060	22.0	101	1	CE	200	52.36
92 X 92 X 25	AD0912LB-A70GL	BALL	12	0.13	1.56	2050	36.0	0.063	25.0	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LB-A702GL	BALL	12	0.12	1.44	2300	41.6	0.087	29.8	101	2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LB-A76GL	BALL	12	0.12	1.44	2300	41.6	0.087	29.8	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912MB-A70GL	BALL	12	0.17	2.04	2600	47.2	0.108	32.7	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912MB-A76GL	BALL	12	0.17	2.04	2600	47.2	0.108	32.7	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912HB-A70GL	BALL	12	0.25	3.00	2900	52.5	0.133	35.0	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HB-A76GL	BALL	12	0.25	3.00	2900	52.5	0.133	35.0	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912UB-A71GL	BALL	12	0.39	4.68	3300	60.0	0.166	39.4	101	1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912UB-A76GL	BALL	12	0.39	4.68	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912XB-A71GL	BALL	12	0.55	6.60	3800	67.0	0.198	43.9	101	1	CE	200	52.36
92 X 92 X 25	AD0912DS-A70GL	S	12	0.09	1.08	1600	28.0	0.060	22.0	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912DS-A71GL	S	12	0.07	1.08	1600	28.0	0.060	22.0	101	1	CE	200	52.36
92 X 92 X 25	AD0912LS-A70GL	S	12	0.13	1.56	2000	32.4	0.054	23.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LS-A73GL	S	12	0.13	1.56	2100	37.9	0.073	26.5	101	3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912LS-A76GL	S	12	0.13	1.56	2000	32.4	0.054	23.5	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912MS-A70GL	S	12	0.17	2.04	2350	43.0	0.087	31.0	101	0,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912MS-A76GL	S	12	0.17	2.04	2350	43.0	0.087	31.0	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912HS-A70GL	S	12	0.25	3.00	2700	50.0	0.117	33.7	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912HS-A76GL	S	12	0.25	3.00	2700	50.0	0.117	33.7	101	6	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0912US-A70GL	S	12	0.39	4.68	3200	57.8	0.156	39.4	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912US-A71GL	S	12	0.39	4.68	3300	60.0	0.198	39.1	101	1,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0912US-A76GL	S	12	0.30	3.60	3300	60.0	0.166	39.4	101	6	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LX-A70GL	HYPRO	24	0.08	1.92	2100	37.9	0.073	26.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924MX-A70GL	HYPRO	24	0.12	2.88	2400	43.5	0.094	31.3	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924MX-A71GL	HYPRO	24	0.17	2.04	2700	43.2	0.140	35.0	101	1	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HX-A70GL	HYPRO	24	0.15	3.60	2700	50.0	0.115	33.7	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924UX-A71GL	HYPRO	24	0.21	5.04	3200	57.8	0.156	38.6	101	1,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924UX-A73GL	HYPRO	24	0.21	5.04	3200	57.8	0.156	38.6	101	3	CE	200	52.36
92 X 92 X 25	AD0924LB-A70GL	BALL	24	0.08	1.92	2100	37.9	0.074	26.5	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LB-A72GL	BALL	24	0.08	1.92	2300	41.6	0.086	29.8	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924LB-A76GL	BALL	24	0.08	1.92	2300	41.6	0.086	29.8	101	6	CE	200	52.36
92 X 92 X 25	AD0924MB-A70GL	BALL	24	0.12	2.88	2600	47.2	0.106	32.7	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HB-A70GL	BALL	24	0.15	3.60	2900	52.5	0.131	35.0	101	0,1,2,3	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HB-A76GL	BALL	24	0.15	3.60	2900	52.5	0.131	35.0	101	6	CE	200	52.36
92 X 92 X 25	AD0924UB-A72GL	BALL	24	0.21	5.04	3300	60.0	0.166	39.4	101	2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924XB-A71GL	BALL	24	0.25	6.00	3800	66.9	0.186	42.6	101	1,2	CE	200	25.36
92 X 92 X 25	AD0924LS-A70GL	S	24	0.08	1.92	2100	37.9	0.073	26.5	101	0,2	CE	200	52.36
92 X 92 X 25	AD0924MS-A70GL	S	24	0.12	2.88	2400	43.5	0.094	31.3	101	0,2	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HS-A70GL	S	24	0.15	3.60	2700	48.0	0.115	33.7	101	0	UL,CUL,TUV,CE	200	52.36
92 X 92 X 25	AD0924HS-A72GL	S	24	0.20	4.80	3000	48.4	0.169	38.0	101	2	UL,CUL,CE	200	52.36
92 X 92 X 25	AD0924HS-A73GL	S	24	0.20	4.80	3000	48.4	0.169	38.0	101	3	UL,CUL,TUV,CE	200	52.36

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED