



SCHMATIC DIAGRAM



General Tolerance Dimemssion

≤ 3	± 0.1
> 3 -10	± 0.2
> 10 -30	± 0.3



Safety authentication



Date	Rev.	Description

Specifications

RATINGS	4A30VDC 1/4hp 250V~25T125 μ 5E4
TEMPERATURE	5GPA125/250V~25T125 μ 5E4
ELECTRONICAL LIFE	5(2)A250V~25T125 μ 5E4 4A30VDC
INSULATION STRENGTH	100MΩ MIN
TEST VOLTAGE	AC1000V/1500V
CONTACT RESISTANCE	50mΩ MAX
OPERATING FORCE	0.4N MAX
OPERATING POSITION	15.2 ± 1 mm
FREE POSITION	19mm MAX

Parts List

No.	Name	Material
1	NC terminal	Brass alloy H65, Silver plated
2	CASE	Plastic PBT
3	NO terminal	Brass alloy H65, Silver plated
4	COVER	Plastic PBT
5	TERMINAL	Brass alloy H65, Silver plated
6	Plunger	Plastic PPS
7	Pull spring	SUS304H
8	Moving arm	Stainless steel SUS304
9	Moving piece	Tin-brass QSn6.5-0.1
10	Contact	AgNi10
11	Contact	AgNi10
12	Roller	leaded brass bars, Nickel plated, NPBS9-1
13	Pin shaft	Brass alloy H62, Nickel plated

GOLDSUN ELECTRONICS CO., LTD.

PART NO. **2333135** Rev. 1

Description :

UNIT mm SCALE SHEET 1 OF 1 CAS No: ERN No:

DRAWN : Jay

VERIFY : Arthur / Sam

DCC. NO.
A4 DRAWING NO.