

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

**2N5457, 2N5458**

Preferred Device

**JFETs - General Purpose**

**N- Channel - Depletion**

N-Channel Junction Field Effect Transistors, depletion mode (Type A) designed for audio and switching applications.

- N-Channel for Higher Gain
- Drain and Source Interchangeable
- High AC Input Impedance
- High DC Input Resistance
- Low Transfer and Input Capacitance
- Low Cross-Modulation and Intermodulation Distortion
- Unibloc Plastic Encapsulated Package



**MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	25	Vdc
Drain - Gate Voltage	$V_{DG}$	25	Vdc
Reverse Gate - Source Voltage	$V_{GSR}$	-25	Vdc
Gate Current	$I_G$	10	mAdc
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above $25^\circ\text{C}$	$P_D$	310 2.82	mW mW/ $^\circ\text{C}$
Operating Junction Temperature	$T_J$	135	$^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	- 65 to +150	$^\circ\text{C}$




**ON Semiconductor®**

<http://onsemi.com>



**TO-92  
CASE 29  
STYLE 5**

**MARKING DIAGRAMS**



Y = Year  
WW = Work Week

**ORDERING INFORMATION**

Device	Package	Shipping
2N5457	TO-92	5000 Units/Box
2N5458	TO-92	5000 Units/Box

**Preferred** devices are recommended choices for future use and best overall value.

## 2N5457, 2N5458

### ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>						
Gate-Source Breakdown Voltage (I <sub>G</sub> = -10 μAdc, V <sub>DS</sub> = 0)		V <sub>(BR)GSS</sub>	-25	-	-	Vdc
Gate Reverse Current (V <sub>GS</sub> = -15 Vdc, V <sub>DS</sub> = 0) (V <sub>GS</sub> = -15 Vdc, V <sub>DS</sub> = 0, T <sub>A</sub> = 100°C)		I <sub>GSS</sub>	-	-	-1.0 -200	nAdc
Gate-Source Cutoff Voltage (V <sub>DS</sub> = 15 Vdc, i <sub>D</sub> = 10 nAdc)	2N5457 2N5458	V <sub>GS(off)</sub>	-0.5 -1.0	-	-6.0 -7.0	Vdc
Gate-Source Voltage (V <sub>DS</sub> = 15 Vdc, i <sub>D</sub> = 100 μAdc) (V <sub>DS</sub> = 15 Vdc, i <sub>D</sub> = 200 μAdc)	2N5457 2N5458	V <sub>GS</sub>	-	-2.5 -3.5	-	Vdc
<b>ON CHARACTERISTICS</b>						
Zero-Gate-Voltage Drain Current (Note 1) (V <sub>DS</sub> = 15 Vdc, V <sub>GS</sub> = 0)	2N5457 2N5458	I <sub>DSS</sub>	1.0 2.0	3.0 6.0	5.0 9.0	mAdc
<b>DYNAMIC CHARACTERISTICS</b>						
Forward Transfer Admittance (Note 1) (V <sub>DS</sub> = 15 Vdc, V <sub>GS</sub> = 0, f = 1 kHz)	2N5457 2N5458	Y <sub>fs</sub>	1000 1500	3000 4000	5000 5500	μmhos
Output Admittance Common Source (Note 1) (V <sub>DS</sub> = 15 Vdc, V <sub>GS</sub> = 0, f = 1 kHz)		Y <sub>os</sub>	-	10	50	μmhos
Input Capacitance (V <sub>DS</sub> = 15 Vdc, V <sub>GS</sub> = 0, f = 1 kHz)		C <sub>iss</sub>	-	4.5	7.0	pF
Reverse Transfer Capacitance (V <sub>DS</sub> = 15 Vdc, V <sub>GS</sub> = 0, f = 1 kHz)		C <sub>rss</sub>	-	1.5	3.0	pF

1. Pulse Width ≤ 630 ms, Duty Cycle ≤ 10%.

# 2N5457, 2N5458

## TYPICAL CHARACTERISTICS For 2N5457 Only




Figure 1. Noise Figure versus Source Resistance




Figure 2. Typical Drain Characteristics




Figure 3. Common Source Transfer Characteristics

# 2N5457, 2N5458

## TYPICAL CHARACTERISTICS For 2N5457 Only




Figure 4. Typical Drain Characteristics




Figure 5. Common Source Transfer Characteristics




Figure 6. Typical Drain Characteristics






Figure 7. Common Source Transfer Characteristics

NOTE: Note: Graphical data is presented for dc conditions. Tabular data is given for pulsed conditions (Pulse Width = 630 ms, Duty Cycle = 10%). Under dc conditions, self heating in higher  $I_{DSS}$  units reduces  $I_{DSS}$ .

# 2N5457, 2N5458

## PACKAGE DIMENSIONS

TO-92 (TO-226)  
CASE 29-11  
ISSUE AL




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---

### TYLE 5:

- PIN 1. DRAIN
- SOURCE
- GATE

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

## PUBLICATION ORDERING INFORMATION

### Literature Fulfillment:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** ONlit@hibbertco.com

**N. American Technical Support:** 800-282-9855 Toll Free USA/Canada

**JAPAN:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

For additional information, please contact your local Sales Representative.