




Dimensions: mm and (In.)






Nut 1 PC

Washer 1 PC t=0.4

R1: 1 2 3
R2: ① ② ③



Terminal Detail



P.C.B. Mounting Hole Detail

Specifications:

• Electrical Characteristics:

Overall resistance range: 1KΩ~1MΩ (tolerance±20%)

Power rating: 0.05W (tolerance±30%)

Taper: **Linear**

Rotation noise (refer to JIS): 100mV max. (W :250mV max)

Insulation resistance: 100MΩ min. at DC 250 volts

Dielectric test: Units shall be designed to withstand 300V AC between resistance elements and case for a period of one minute without damage or arcing.

Maximum operating voltage: **50V AC** this potentiometer is designed for AC voltage only.

• Endurance Characteristics:

Rotational life: More than 15,000 cycles