





Dimensions: mm and (In.)




Terminal Detail

R1: 1 2 3  
R2: ① ② ③



**Specifications:**

- Mechanical Characteristics:
  - Overall rotation angle: 300±5°
- Electrical Characteristics:
  - Overall resistance range: 1KΩ~1MΩ (tolerance±20%)
  - Power rating: **0.05W (tolerance±30%)**
  - Taper: **Audio**
  - Rotation noise (refer to JIS): 100mV max. (W :250mV max)
  - Insulation resistance: 100MΩ min. at DC 250 volts
  - Dielectric test: Units shall be designed to withstand 300V AC between resistance elements and case for a period of one minute without damage or arcing.
  - Maximum operating voltage: **50V AC** this potentiometer is designed for AC voltage only.
- Endurance Characteristics:
  - Rotational life: More than 15,000 cycles



P.C.B. Mounting Hole Detail