

Model	Outline Drawing	Features / Individual Specification															
RV012AF-20 	<p>SHAFT SHOWN IN FULL C.C.W. POSITION.</p>	<table border="1"> <thead> <tr> <th>Terminal Type</th> <th>H</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>20</td> <td>10</td> <td>3</td> </tr> <tr> <td>22</td> <td>10</td> <td>4</td> </tr> <tr> <td>23</td> <td>13.5</td> <td>3</td> </tr> <tr> <td>24</td> <td>12.5</td> <td>3</td> </tr> </tbody> </table>	Terminal Type	H	A	20	10	3	22	10	4	23	13.5	3	24	12.5	3
Terminal Type	H	A															
20	10	3															
22	10	4															
23	13.5	3															
24	12.5	3															
RV012AF-40 	<p>SHAFT SHOWN IN FULL C.C.W. POSITION.</p>																

SHAFT STYLE AND DIMENSIONS

Horizontal	Terminal Type	K TYPE	B TYPE	F TYPE
	20			
	22			
	24			
	40			
Vertical				

RV120DF-40-(L)A 	<p>SHAFT SHOWN IN FULL C.C.W. POSITION</p>	
----------------------------	--	--

SPECIFICATION

	RV012AF	RV120DF
MECHANICAL		
TOTAL ROTATION ANGLE	300°±5°	300°±5°
ROTATION TORQUE	20-150 gf.cm	20-150 gf.cm
SHAFT STOP STRENGTH	4kgf.cm/min.	4kgf.cm/min.
CLICK POSITION	center click	center click
CLICK TORQUE	50-200gf.cm	50-300gf.cm
ELECTRICAL		
RATED WATTAGE	0.08W	0.08W
RATED VOLTAGE	150V	150V
INSULATION RESISTANCE	more than 50M Ω at 500V DC	more than 50M Ω at 250V DC
DIELECTRIC STRENGTH	500VAC, 1minute	250VAC, 1minute
ROTATION LIFE	15,000 cycles	15,000 cycles