

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 10	AD0405HS-G70	S	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HS-G7B	S	5	0.15	0.75	6000	6.7	0.100	25.0	24	0	CE	700	
40 X 40 X 10	AD0409HS-G70	S	9	0.13	1.17	6000	6.8	0.100	25.0	24	0	UL,CE	700	
40 X 40 X 10	AD0409LS-G70	S	9	0.08	0.72	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0409MS-G70	S	9	0.10	0.90	4800	5.6	0.080	19.0	24	0	CE	700	
40 X 40 X 10	AD0409US-G70	S	9	0.15	1.35	7000	7.7	0.068	29.7	24	0	CE	700	
40 X 40 X 10	AD0412DX-G70	HYPRO	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LX-G70	HYPRO	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MX-G70	HYPRO	12	0.08	0.96	4800	5.7	0.078	19.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G70	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HX-G71	HYPRO	12	0.10	1.20	6000	6.7	0.100	25.0	24	1	CE	700	
40 X 40 X 10	AD0412DB-G70	BALL	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LB-G70	BALL	12	0.07	0.84	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G70	BALL	12	0.08	0.96	5000	5.9	0.080	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MB-G72	BALL	12	0.09	1.08	5000	6.0	0.080	20.0	24	2	CE	700	
40 X 40 X 10	AD0412MB-G73	BALL	12	0.09	1.08	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0412HB-G70	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G70(U)	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HB-G72	BALL	12	0.10	1.20	6000	6.7	0.100	25.0	24	2,3	CE	700	
40 X 40 X 10	AD0412UB-G70	BALL	12	0.10	1.20	6800	7.9	0.129	28.0	24	0,6	CE	700	
40 X 40 X 10	AD0412DS-G70	S	12	0.07	0.84	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0412LS-G70	S	12	0.07	0.84	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412MS-G70	S	12	0.08	0.96	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0412HS-G70	S	12	0.10	1.20	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LX-G70(T)	HYPRO	24	0.07	1.68	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MX-G70	HYPRO	24	0.05	1.20	4200	4.7	0.068	17.2	24	0	CE	700	
40 X 40 X 10	AD0424MX-G70(T)	HYPRO	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HX-G70	HYPRO	24	0.09	2.16	6000	6.8	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HX-G76(T)	HYPRO	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LB-G70	BALL	24	0.07	1.68	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G70	BALL	24	0.08	1.92	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MB-G76	BALL	24	0.08	1.92	5000	5.9	0.080	20.0	24	6	CE	700	
40 X 40 X 10	AD0424HB-G70	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HB-G76	BALL	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424LS-G70	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	0	CE	700	
40 X 40 X 10	AD0424LS-G76	S	24	0.07	1.68	4200	4.7	0.060	14.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424MS-G70	S	24	0.08	1.92	4800	5.7	0.078	20.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0424HS-G70	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	0	UL,CUL,CSA,TUV,CE	700	
40 X 40 X 10	AD0424HS-G76	S	24	0.09	2.16	6000	6.7	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 15	AD0412LX-D50	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	0	CE	700	44.00
40 X 40 X 15	AD0412LX-D52	HYPRO	12	0.10	1.20	6000	6.8	0.161	30.3	27	2	UL,CUL,TUV,CE	700	44.00
40 X 40 X 15	AD0412LX-D56	HYPRO	12	0.08	0.96	6000	6.8	0.161	30.3	27	6	UL,CUL,CE	700	44.00
40 X 40 X 15	AD0412MX-D50	HYPRO	12	0.10	1.20	7000	8.1	0.210	31.8	27	0,6	UL,CUL,CE	500	44.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED