

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**


The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 36265VIS



General Purpose Plastic Rectifiers

Reverse Voltage  
50 to 1000V  
Forward Current 3.0A



Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- High surge current capability
- Construction utilizes void-free molded plastic technique
- 3.0 Ampere operation at  $T_L=105^\circ\text{C}$  with no thermal runaway
- Typical  $I_r$  less than  $0.1\mu\text{A}$
- High temperature soldering guaranteed:  $250^\circ\text{C}/10$  seconds,  $0.375"$  (9.5mm) lead length, 5 lbs. (2.3kg) tension

Mechanical Data

**Case:** JEDEC DO-201AD, molded plastic body  
**Terminals:** Plated axial leads, solderable per MIL-STD-750, Method 2026  
**Polarity:** Color band denotes cathode end  
**Mounting Position:** Any  
**Weight:** 0.04 oz., 1.1 g

Maximum Ratings & Thermal Characteristics Ratings at  $25^\circ\text{C}$  ambient temperature unless otherwise specified.

Parameter	Symb.	1N 5400	1N 5401	1N 5402	1N 5403	1N 5404	1N 5405	1N 5406	1N 5407	1N 5408	Unit
* Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	300	400	500	600	800	1000	V
* Maximum RMS voltage	$V_{RMS}$	35	70	140	210	280	350	420	560	700	V
* Maximum DC blocking voltage to $T_A = 150^\circ\text{C}$	$V_{DC}$	50	100	200	300	400	500	600	800	1000	V
* Maximum average forward rectified current $0.5"$ (12.5mm) lead length at $T_L = 105^\circ\text{C}$	$I_{F(AV)}$	3.0									A
* Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) at $T_L=105^\circ\text{C}$	$I_{FSM}$	200									A
* Maximum full load reverse current, full cycle average $0.5"$ (12.5mm) lead length at $T_L = 105^\circ\text{C}$	$I_{R(AV)}$	500									$\mu\text{A}$
* Typical thermal resistance <sup>(1)</sup>	$R_{\theta JA}$	20									$^\circ\text{C}/\text{W}$
Maximum DC blocking voltage temperature	$T_A$	+150									$^\circ\text{C}$
* Operating junction and storage temperature range	$T_J, T_{STG}$	-50 to +170									$^\circ\text{C}$

Electrical Characteristics Ratings at  $25^\circ\text{C}$  ambient temperature unless otherwise specified.

* Maximum instantaneous forward voltage at 3.0A	$V_F$	1.2									V
* Maximum DC reverse current at rated DC blocking voltage	$I_R$	$T_A = 25^\circ\text{C}$ $T_A = 150^\circ\text{C}$									$\mu\text{A}$
Typical junction capacitance at 4.0V, 1MHz	$C_J$	30									pF

**Note:** (1) Thermal resistance from junction to ambient at  $0.375"$  (9.5mm) lead length, P.C.B. mounted with  $0.8 \times 0.8"$  (20 x 20mm) copper heatsinks  
 \*JEDEC registered values


# 1N5400 thru 1N5408

Vishay Semiconductors  
formerly General Semiconductor




## Ratings and Characteristic Curves ( $T_A = 25^\circ\text{C}$ unless otherwise noted)


**Fig. 1 — Forward Current Derating Curve**




**Fig. 2 — Maximum Non-Repetitive Peak Forward Surge Current**




**Fig. 3 — Typical Instantaneous Forward Characteristics**




**Fig. 4 — Typical Reverse Characteristics**



**Fig. 5 — Typical Junction Capacitance**



**Fig. 6 — Typical Transient Thermal Impedance**



This datasheet has been download from:

[www.datasheetcatalog.com](http://www.datasheetcatalog.com)

Datasheets for electronics components.