

ADDA USA
DC FAN SPECIFICATIONS

| Frame Dimensions (mm) | Model Part Number | Bearing Type | Volts (V) | Current (A) | Power (W) | Speed (RPM) | Air Flow (CFM) | Pressure (Inches) | Noise (dB/A) | Weight (g) | Features Available | Safety Approvals | Units Per Box | Box Wt. (lbs.) |
|-----------------------|-------------------|--------------|-----------|-------------|-----------|-------------|----------------|-------------------|--------------|------------|--------------------|------------------|---------------|----------------|
| 40 X 40 X 6 | AD0405LX-KC0 | HYPRO | 5 | 0.11 | 0.55 | 4500 | 3.6 | 0.061 | 22.4 | 9 | 0 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405LX-KC3 | HYPRO | 5 | 0.08 | 0.40 | 4500 | 4.6 | 0.068 | 27.1 | 9 | 3 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MX-K90 | HYPRO | 5 | 0.09 | 0.45 | 5500 | 5.2 | 0.064 | 23.8 | 9 | 0,6 | UL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MX-KC0 | HYPRO | 5 | 0.20 | 1.00 | 5500 | 4.6 | 0.093 | 28.6 | 9 | 0,3 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MX-KC3(Y) | HYPRO | 5 | 0.11 | 0.55 | 5500 | 4.6 | 0.093 | 28.6 | 9 | 3 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405HX-K90 | HYPRO | 5 | 0.12 | 0.60 | 6300 | 6.0 | 0.079 | 27.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405HX-KC0 | HYPRO | 5 | 0.23 | 1.15 | 6000 | 5.0 | 0.110 | 31.2 | 9 | 0 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405HX-KC3 | HYPRO | 5 | 0.13 | 0.65 | 6000 | 5.0 | 0.110 | 31.2 | 9 | 3 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405LB-K90(S) | 1B,1S | 5 | 0.05 | 0.25 | 4800 | 4.5 | 0.051 | 19.9 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MB-K90(S) | 1B,1S | 5 | 0.09 | 0.45 | 5800 | 5.5 | 0.067 | 25.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MB-KC3 | BALL | 5 | 0.11 | 0.55 | 5800 | 4.9 | 0.102 | 30.0 | 9 | 3 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405HB-K90(S) | 1B,1S | 5 | 0.12 | 0.60 | 6600 | 6.0 | 0.090 | 30.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0405MS-K90 | S | 5 | 0.09 | 0.45 | 5500 | 5.2 | 0.064 | 23.8 | 9 | 0 | CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412LX-K90 | HYPRO | 12 | 0.06 | 0.72 | 4500 | 4.4 | 0.049 | 20.9 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412MX-K90 | HYPRO | 12 | 0.06 | 0.72 | 5500 | 5.2 | 0.064 | 23.8 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412HX-K90 | HYPRO | 12 | 0.08 | 0.96 | 6300 | 5.9 | 0.079 | 27.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412LB-K90(S) | 1B,1S | 12 | 0.06 | 0.72 | 4800 | 4.7 | 0.049 | 21.6 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412MB-K90(S) | 1B,1S | 12 | 0.06 | 0.72 | 5800 | 5.5 | 0.067 | 25.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 6 | AD0412HB-K90(S) | 1B,1S | 12 | 0.08 | 0.96 | 6600 | 6.0 | 0.090 | 30.0 | 9 | 0,6 | UL,CUL,TUV,CE | 400 | 13.20 |
| 40 X 40 X 8 | AD0405LX-J90 | HYPRO | 5 | 0.12 | 0.60 | 4100 | 5.1 | 0.058 | 20.0 | 5 | 0 | CE | | |
| 40 X 40 X 8 | AD0405MX-J90 | HYPRO | 5 | 0.16 | 0.80 | 5500 | 6.3 | 0.094 | 28.7 | 5 | 0 | CE | | |
| 40 X 40 X 8 | AD0405MX-J93 | HYPRO | 5 | 0.15 | 0.75 | 5500 | 6.8 | 0.098 | 29.0 | 5 | 3 | CE | | |
| 40 X 40 X 8 | AD0405HX-J91 | HYPRO | 5 | 0.23 | 1.15 | 6000 | 7.5 | 0.110 | 31.0 | 5 | 1,3 | CE | | |
| 40 X 40 X 8 | AD0405MB-J90 | BALL | 5 | 0.20 | 1.00 | 5000 | 6.1 | 0.089 | 26.0 | 5 | 0 | CE | | |
| 40 X 40 X 8 | AD0412MX-J90 | HYPRO | 12 | 0.13 | 1.56 | 5000 | 6.1 | 0.089 | 26.0 | 5 | 0 | CE | | |
| 40 X 40 X 9 | AD0405HX-RA3 | HYPRO | 5 | 0.25 | 1.25 | 6000 | 3.1 | 0.334 | 40.3 | 5 | 3 | CE | | |
| 40 X 40 X 10 | AD0405DX-G70 | HYPRO | 5 | 0.07 | 0.35 | 3300 | 3.8 | 0.044 | 14.5 | 24 | 0 | CE | 700 | |
| 40 X 40 X 10 | AD0405LX-G70 | HYPRO | 5 | 0.08 | 0.40 | 4200 | 4.7 | 0.060 | 14.0 | 24 | 0 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405LX-G76 | HYPRO | 5 | 0.08 | 0.40 | 4200 | 4.7 | 0.060 | 14.0 | 24 | 6 | UL,CUL,CE | 700 | |
| 40 X 40 X 10 | AD0405MX-G70 | HYPRO | 5 | 0.11 | 0.55 | 4800 | 5.7 | 0.780 | 19.0 | 24 | 0 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405MX-G7 | HYPRO | 5 | 0.11 | 0.55 | 4800 | 5.7 | 0.078 | 20.0 | 24 | 6 | UL,CUL,CE | 700 | |
| 40 X 40 X 10 | AD0405HX-G70 | HYPRO | 5 | 0.19 | 0.95 | 6000 | 6.7 | 0.100 | 25.0 | 24 | 0,6 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405DB-G70 | BALL | 5 | 0.07 | 0.35 | 3300 | 3.8 | 0.044 | 14.5 | 24 | 0 | CE | 700 | |
| 40 X 40 X 10 | AD0405LB-G70 | BALL | 5 | 0.08 | 0.40 | 4600 | 5.0 | 0.060 | 14.0 | 24 | 0,6 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405MB-G70 | BALL | 5 | 0.11 | 0.55 | 4800 | 5.7 | 0.078 | 20.0 | 24 | 0 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405MB-G72 | BALL | 5 | 0.15 | 0.75 | 4800 | 5.7 | 0.078 | 20.0 | 24 | 2 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405MB-G73 | BALL | 5 | 0.15 | 0.75 | 4800 | 5.7 | 0.078 | 20.0 | 24 | 3 | CE | 700 | |
| 40 X 40 X 10 | AD0405MB-G76 | BALL | 5 | 0.11 | 0.55 | 5000 | 6.0 | 0.080 | 20.0 | 24 | 6 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405HB-G70 | BALL | 5 | 0.19 | 0.95 | 6000 | 6.8 | 0.100 | 25.0 | 24 | 0 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405HB-G72 | BALL | 5 | 0.25 | 1.25 | 6000 | 6.7 | 0.100 | 25.0 | 24 | 2 | CE | 700 | |
| 40 X 40 X 10 | AD0405HB-G76 | BALL | 5 | 0.19 | 0.95 | 6000 | 6.8 | 0.100 | 25.0 | 24 | 6 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405LS-G70 | S | 5 | 0.08 | 0.40 | 4200 | 4.7 | 0.060 | 14.0 | 24 | 0,6 | UL,CUL,TUV,CE | 700 | |
| 40 X 40 X 10 | AD0405MS-G70 | S | 5 | 0.11 | 0.55 | 4800 | 5.7 | 0.078 | 20.0 | 24 | 0,2,6 | UL,CUL,TUV,CE | 700 | |

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED