

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 20	AD0412UB-C50	BALL	12	0.14	1.68	8500	10.6	0.325	36.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412DS-C56	S	12	0.05	0.60	3700	4.7	0.064	10.0	27	6	UL,CUL,CE	500	36.96
40 X 40 X 20	AD0412LS-C50	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LS-C56	S	12	0.07	0.84	6000	7.5	0.154	23.9	27	6	CE	500	36.96
40 X 40 X 20	AD0412MS-C50	S	12	0.08	0.96	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C50	S	12	0.11	1.32	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HS-C52	S	12	0.15	1.80	7500	9.6	0.240	31.0	28	2	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412US-C50	S	12	0.14	1.68	8200	10.3	0.305	35.0	28	0	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LX-C50	B or S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MX-C50	B or S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HX-C50	B or S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LB-C50	BALL	24	0.06	1.44	6200	7.7	0.165	25.0	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MB-C50	BALL	24	0.07	1.68	6900	8.5	0.190	28.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HB-C50	BALL	24	0.09	2.16	7800	10.1	0.263	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LS-C50	S	24	0.06	1.44	6000	7.5	0.154	23.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MS-C50	S	24	0.07	1.68	6700	8.3	0.180	27.5	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HS-C50	S	24	0.09	2.16	7500	9.6	0.240	31.0	27	0,6	UL,CUL,TUV,CE	500	36.96
45 X 45 X 6	AD4505LX-K90	HYPRO	5	0.10	0.50	4300	6.2	0.056	23.0	24	0	CE	560	19.30
45 X 45 X 6	AD4505MX-K90	HYPRO	5	0.12	0.60	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HX-K90	HYPRO	5	0.14	0.70	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505LB-K90(S)	1B & 1S	5	0.10	0.50	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505MB-K90(S)	1B & 1S	5	0.12	0.60	5500	7.2	0.085	26.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4505HB-K90(S)	1B & 1S	5	0.14	0.70	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LX-K90	HYPRO	12	0.08	0.96	4300	6.2	0.056	23.0	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MX-K90	HYPRO	12	0.09	1.08	5000	7.1	0.074	25.5	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512HX-K90	HYPRO	12	0.10	1.20	6000	9.2	0.103	32.6	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512LB-K90(S)	1B & 1S	12	0.08	0.96	4500	6.5	0.059	23.3	24	0,6	CE	560	19.30
45 X 45 X 6	AD4512MB-K90(S)	1B & 1S	12	0.09	1.08	5500	7.2	0.085	26.5	24	0	CE	560	19.30
45 X 45 X 6	AD4512HB-K90(S)	1B & 1S	12	0.10	1.20	6200	9.5	0.111	33.0	24	0,6	CE	560	19.30
45 X 45 X 7	AD4505MX-QA0	HYPRO	5	0.09	0.45	5000	1.6	0.224	25.5	23	0	CE	480	
45 X 45 X 7	AD4505HX-QA0	HYPRO	5	0.14	0.70	5700	1.8	0.332	28.5	23	0,6	CE	480	
45 X 45 X 7	AD4505HX-QA3	HYPRO	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 7	AD4505HB-QA3	BALL	5	0.12	0.60	6200	2.1	0.397	31.2	23	3	CE	480	
45 X 45 X 9	AD4505HX-RB3	HYPRO	5	0.22	1.10	4500	3.1	0.213	31.8	26	3	CE	500	
45 X 45 X 10	AD4505LX-G70(T)	HYPRO	5	0.16	0.80	3800	6.8	0.062	17.5	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-G70	HYPRO	5	0.10	0.50	4200	6.9	0.069	21.6	24	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-G70(T)	HYPRO	5	0.18	0.90	4500	7.5	0.078	22.0	24	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-GD0	HYPRO	5	0.25	1.25	4200	2.0	0.290	22.0	26	0,6	CE	500	24.64
45 X 45 X 10	AD4505MX-GD1	HYPRO	5	0.15	0.75	5000	2.3	0.342	31.1	26	1	CE	500	24.64
45 X 45 X 10	AD4505HX-G70	HYPRO	5	0.20	1.00	5500	9.1	0.107	27.4	24	0	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505HX-G76	HYPRO	5	0.20	1.00	5500	9.1	0.109	28.6	24	6	CE	500	24.64
45 X 45 X 10	AD4505HX-GD0	HYPRO	5	0.22	1.10	5200	2.7	0.434	27.4	26	0,3	CE	500	24.64
45 X 45 X 10	AD4505HX-GD1	HYPRO	5	0.17	0.85	4800	7.0	0.050	28.9	26	1	CE	500	24.64

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED