


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.


Jameco Part Number 36273VIS



General Purpose Plastic Rectifiers

Reverse Voltage
50 to 1000V
Forward Current 3.0A

DO-201AD



Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- High surge current capability
- Construction utilizes void-free molded plastic technique
- 3.0 Ampere operation at $T_L=105^\circ\text{C}$ with no thermal runaway
- Typical I_R less than $0.1\mu\text{A}$
- High temperature soldering guaranteed: $250^\circ\text{C}/10$ seconds, $0.375"$ (9.5mm) lead length, 5 lbs. (2.3kg) tension

Mechanical Data

Case: JEDEC DO-201AD, molded plastic body
Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026
Polarity: Color band denotes cathode end
Mounting Position: Any
Weight: 0.04 oz., 1.1 g

Maximum Ratings & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symb.	1N 5400	1N 5401	1N 5402	1N 5403	1N 5404	1N 5405	1N 5406	1N 5407	1N 5408	Unit
* Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	300	400	500	600	800	1000	V
* Maximum RMS voltage	V_{RMS}	35	70	140	210	280	350	420	560	700	V
* Maximum DC blocking voltage to $T_A = 150^\circ\text{C}$	V_{DC}	50	100	200	300	400	500	600	800	1000	V
* Maximum average forward rectified current $0.5"$ (12.5mm) lead length at $T_L = 105^\circ\text{C}$	$I_{F(AV)}$	3.0									A
* Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) at $T_L=105^\circ\text{C}$	I_{FSM}	200									A
* Maximum full load reverse current, full cycle average $0.5"$ (12.5mm) lead length at $T_L = 105^\circ\text{C}$	$I_{R(AV)}$	500									μA
* Typical thermal resistance ⁽¹⁾	$R_{\theta JA}$	20									$^\circ\text{C}/\text{W}$
Maximum DC blocking voltage temperature	T_A	+150									$^\circ\text{C}$
* Operating junction and storage temperature range	T_J, T_{STG}	-50 to +170									$^\circ\text{C}$

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

* Maximum instantaneous forward voltage at 3.0A	V_F	1.2									V
* Maximum DC reverse current at rated DC blocking voltage	I_R	$T_A = 25^\circ\text{C}$ $T_A = 150^\circ\text{C}$									μA
Typical junction capacitance at 4.0V, 1MHz	C_J	30									pF

Note: (1) Thermal resistance from junction to ambient at $0.375"$ (9.5mm) lead length, P.C.B. mounted with $0.8 \times 0.8"$ (20 x 20mm) copper heatsinks
*JEDEC registered values

1N5400 thru 1N5408

Vishay Semiconductors
formerly General Semiconductor



Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 — Forward Current Derating Curve




Fig. 2 — Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 — Typical Instantaneous Forward Characteristics




Fig. 4 — Typical Reverse Characteristics




Fig. 5 — Typical Junction Capacitance





Fig. 6 — Typical Transient Thermal Impedance



This datasheet has been download from:

www.datasheetcatalog.com

Datasheets for electronics components.