

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.



Jameco Part Number 252401

50W Single Output Switching Power Supply

LPS-50 series

MODEL LPS-50-12

OUTPUT FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	RIPPLE & NOISE	V1: 80 mVp-p (Max)	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	V1: 8 mVp-p (Max)	P
2	OUTPUT VOLTAGE ADJUST RANGE	CH1: 10.8V~ 13.2 V (TYP)	I/P: 230 VAC I/P: 115 VAC O/P:MIN LOAD Ta:25°C	10.15V~ 13.73 V/ 230VAC 10.15V~13.73 V/ 115VAC	P
3	OUTPUT VOLTAGE TOLERANCE	V1: -2%~ 2% (Max)	I/P: 90 VAC / 264 VAC O/P:FULL/ 0% LOAD Ta:25°C	V1: 0.03%~ -0.03%	P
4	LINE REGULATION	V1: -1%~ 1% (Max)	I/P: 90 VAC ~ 264 VAC O/P:FULL LOAD Ta:25°C	V1: 0%~ -0.05%	P
5	LOAD REGULATION	V1: -2%~ 2% (Max)	I/P: 230 VAC O/P:FULL ~MIN LOAD Ta:25°C	V1: 0%~ 0%	P
6	SET UP TIME	230 VAC/ 100 ms (Max) 115 VAC/ 100 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230 VAC/ 18 ms 115 VAC/ 17 ms	P
7	RISE TIME	230 VAC/ 40 ms (Max) 115 VAC/ 40 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230 VAC/ 11 ms 115 VAC/ 11 ms	P
8	HOLD UP TIME	230VAC/ 50 ms (Min) 115VAC/ 12 ms (Min)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230 VAC/ 81 ms 115 VAC/ 17 ms	P
9	OVER/UNDERSHOOT TEST	< ±5%	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	TEST: <5 %	P
10	DYNAMIC LOAD	V1: 1200 mVp-p	I/P: 230 VAC O/P:FULL /Min LOAD 90%DUTY/1KHZ Ta:25°C	103 mVp-p	P

INPUT FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	INPUT VOLTAGE RANGE	90 VAC~ 264 VAC (Typ)	I/P:TESTING O/P:FULL LOAD Ta:25°C	56V~ 264 V	P
			I/P: LOW-LINE-3V= 87 V HIGH-LINE+15%= 300 V O/P:FULL/MIN LOAD ON: 30 Sec . OFF: 30 Sec 10MIN (AC POWER ON/OFF NO DAMAGE)	TEST: OK	
2	INPUT FREQUENCY RANGE	47 HZ ~ 63 HZ (Typ) NO DAMAGE OSC	I/P: 90 VAC ~ 264 VAC O/P:FULL-MIN LOAD Ta:25°C	TEST: OK	P
3	EFFICIENCY	82 % (TYP)	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	83.4 %	P
4	INPUT CURRENT	230 V/ 0.8 A (Max) 115 V/ 1.2 A (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	I = 0.56 A/ 230 VAC I = 0.92 A/ 115VAC	P
5	INRUSH CURRENT	230 V/ 35 A (Max) 115 V/ 25 A (Max) COLD START	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	I = 33.2 A/ 230 VAC I = 18 A/ 115 VAC	P
6	LEAKAGE CURRENT	< 1 mA / 240 VAC	I/P: 254 VAC O/P:Min LOAD Ta:25°C	L-FG: 0.42 mA N-FG: 0.42 mA	P

PROTECTION FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	OVER LOAD PROTECTION	122 %~ 160 %(Typ)	I/P: 230 VAC I/P: 115VAC O/P: TESTING Ta:25°C	142%/230VA 131%/115VAC Hiccup Mode	P
2	OVER VOLTAGE PROTECTION	CH1: 13.8 V~ 16.2 V(Typ)	I/P: 230 VAC I/P: 115 VAC O/P: MIN LOAD Ta:25°C	14.8V/230VAC 14.8V/115VAC Hiccup Model	P
3	SHORT PROTECTION	SHORT EVERY OUTPUT 1 HOUR NO DAMAGE	I/P: 264 VAC O/P: Full LOAD Ta:25°C	NO DAMAGE Hiccup Mode	P

CONTROL FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	REMOTE CONTROL	Rc+ / Rc- 0 V~ 0.8 V POWER ON 4 V~ 10 V POWER OFF	I/P: 230 VAC O/P: FULL LOAD Ta:25°C	0V ~ 3 V POWER ON 3.6V ~ 10 V POWER OFF	P

ENVIRONMENT TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	TEMPERATURE RISE TEST	MODEL : LPS-50-5V 1. ROOM AMBIENT BURN-IN : 1 HRS I/P: 230 VAC O/P: 100% LOAD Ta= 27 °C 2. HIGH AMBIENT BURN-IN : 2 HRS I/P: 230 VAC O/P: 100% LOAD Ta= 53.2 °C			P
2	OVER LOAD BURN-IN TEST	NO DAMAGE 1 HOUR (MIN)	I/P: 230 VAC O/P: 146% Ta:25°C	TEST : OK	P
3	LOW TEMPERATURE TURN ON TEST	TURN ON AFTER 2 HOUR	I/P: 230 VAC O/P: 100 % LOAD Ta= -20 °C	TEST : OK	P
4	HIGH HUMIDITY HIGH TEMPERATURE HIGH VOLTAGE TURN ON TEST	AFTER 12 HOURS IN CHAMBER ON CONTROL 50°C NO DAMAGE	I/P: 272 VAC O/P:FULL LOAD Ta= 50 °C HUMIDITY= 95 %R.H	TEST : OK	P
5	TEMPERATURE COEFFICIENT	± 0.04 % (0~50°C)	I/P: 230 VAC O/P:FULL LOAD	0.01 % (0~50°C)	P
6	VIBRATION TEST	1 Carton & 1 Set Operating at I/P: 230 VAC NO LOAD (1) Waveform: Sine Wave (2) Frequency:10~500Hz (3) Sweep Time:10min/sweep cycle (4) Acceleration:2G (5) Test Time:1 hour in each axis (X.Y.Z) (6) Ta:25°C		TEST : OK	P

SAFETY TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	WITHSTAND VOLTAGE	I/P-O/P: 3 KVAC/min I/P-FG: 1.5 KVAC/min O/P-FG: 0.5 KVAC/min	I/P-O/P: 3.6 KVAC/min I/P-FG: 1.8 KVAC/min O/P-FG: 0.6 KVAC/min Ta:25°C	I/P-O/P: 3.82 mA I/P-FG: 4.29 mA O/P-FG: 2.35 mA NO DAMAGE	P
2	ISOLATION RESISTANCE	I/P-O/P:500VDC>100MΩ I/P-FG: 500VDC>100MΩ O/P-FG:500VDC>100MΩ	I/P-O/P: 500 VDC I/P-FG: 500 VDC O/P-FG: 500 VDC Ta:25°C	I/P-O/P: 30G Ω I/P-FG: 27G Ω O/P-FG: 30G Ω NO DAMAGE	P
3	GROUNDING CONTINUITY	FG(PE) TO CHASSIS OR TRACE < 100 mΩ	30 A / 2min Ta:25°C	16 mΩ	P
4	APPROVAL	TUV: Certificate NO : R50033909 UL: File NO : E183223			P

E.M.C TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	HARMONIC	EN61000-3-2 CLASS A	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	PASS	P
2	CONDUCTION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL/50% LOAD Ta:25°C	PASS Test by certified Lab	P
3	RADIATION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL LOAD Ta:25°C	PASS Test by certified Lab	P
4	E.S.D	EN61000-4-2 INDUSTRY AIR:8KV / Contact:4KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
5	E.F.T	EN61000-4-4 INDUSTRY INPUT: 2KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
6	SURGE	IEC61000-4-5 INDUSTRY L-N :2KV L,N-PE:4KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
7	Test by certified Lab & Test Report Prepare				

M.T.B.F & LIFE CYCLE CALCULATION

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	CAPACITOR LIFE CYCLE	SUPPOSE C 52 IS THE MOST CRITICAL COMPONENT I/P:230VAC O/P:FULL LOAD Ta=25°C LIFE TIME= 119659 HRS I/P:230VAC O/P:FULL LOAD Ta=50°C LIFE TIME= 28706 HRS			P
2	MTBF	MIL-HDBK-217F NOTICES2 PARTS COUNT TOTAL FAILURE RATE: 341.7K HRS			P

COMPONENT STRESS TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	Power Transistor (D to S) or (C to E) Peak Voltage	Q 1 Rated K2645: 600 V 9 A	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 440 V (2) 464 V (3) 480 V	P
2	Diode Peak Voltage	D51 Rated BYQ28X-200 : 200 V 10 A	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 69 V (2) 80 V (3) 70 V	P
3	Clamp Diode Peak Voltage	D1 Rated EGP20J : 600 V 2 A	I/P:High-Line +3V = 267 V O/P: (1)Full Load (2) Dynamic Load 90%Duty/1KHz Ta:25°C	(1) 464 V (2) 464 V	P

DATE	SAMPLE	TEST RESULT	TESTER	APPROVAL
2003/9/24	RD SAMPLE	PASS	VINCENT TSENG	MAX LIN
2003/11/21	PRODUCT SAMPLE A310B03	PASS	VINCENT TSENG	MAX LIN
2004/3/12	PRODUCT SAMPLE A402B03	PASS	VINCENT TSENG	MAX LIN

2003/12/12 A50-F023