

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 495699

Soft Shell Connectors

.250" Centerline, 600 V, 19 - 36 A max. (Universal MATE-N-LOK)

AMP 350547-1 Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 350547-1)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<input type="checkbox"/> General Info	<input type="checkbox"/> Pricing	<input type="checkbox"/> Tooling
<input type="checkbox"/> Sales Info	<input type="checkbox"/> Product Availability	
<input type="checkbox"/> Assembly Subcontractors		

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not relevant for lead free process
Product Type:	Contact
Connector Line:	Universal MATE-N-LOK
CompactPCI:	No
Contact Type:	Pin
High Current:	No
Wire Range (mm [AWG]):	0.50-2.00 ² [20-14]

Other Properties:

RoHS/ELV Compliance History:	Always was compliant
Contact Diameter (mm [in]):	2.13 [0.084]
Stock Thickness (mm [in]):	0.30 [0.012]
Voltage (VAC):	600
Packaging Method:	Loose Piece
Contact Termination Area Plating:	Pre-Tin
Comment:	Contacts can be used with Splash Proof Seals.

Insulation Diameter (mm [in]):	1.52-3.30 [.060-.130]
Contact Material:	Brass
Sealable:	Yes
Current Rating (Amps.):	19

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

