

Date	Rev.	Description

Item	Description
A. Construction - -	
A1. Conductor	A11 No. of conductor 15C
	A12 Material Stranded ; tinned copper wire
	A13 AWG size & composition 24 AWG ( 7 strands / 0.20 mm )
	A14 Diameter Nominal 0.6 mm
A2. Insulation	A21 Material Semi-rigid Polyvinyl chloride (SR-PVC) L.F
	A22 Nom. thickness 0.25 mm
	A23 Nom. diameter 1.1 mm
	A24 Rated Temperature 80 °C
	A25 Rated Voltage 300 V
A3. Shield	A31 Material & Manner Overall Aluminum / polyester tape Wrapped , A1. side faced out.
	A32 Overlap Min. 25 %
A4. Drain wire	A41 Material Stranded ; tinned copper wire
	A42 AWG size & composition 24 AWG ( 7 strands / 0.20 mm )
	A43 Diameter Nominal 0.60 mm
	A44 Note The drain wire is laid in between Aluminum / polyester shield and braid.
A5. Braid	A51 Material
	A52 Size & composition
	A53 Coverage
A6. Jacket	A61 Material Polyvinyl chloride (PVC) L.F
	A62 Nom. thickness 0.8 mm ^
	A63 Overall diameter 7.0 +/- 0.15 mm
A7. Jacket printing	

PAGE 1

DCC. NO.
A4 DRAWING NO.

MATERIAL	<b>GOLDSUN ELECTRONICS CO., LTD.</b>		
	JAMECO NO. <b>644463</b>	GOLDSUN NO. SC15-1000	
DRAWN: Ivan Wang	Description CABLE, SHIELDED, 15 CONDUCTOR, GRAY, 24AWG, 1000FT, ROUND		Rev. 1
VERIFY PEOPLE: Jenny	UNIT: mm	SCALE:	CAS No: ERN No:
		SHEET 1 OF 1	