

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 800577

FEATURES AND SPECIFICATIONS

Features and Benefits

- Exceeds Category 5 performance
- Gigabit Ethernet compatible
- Enclosed top
- Industry Standard Footprint
- Shield with enhanced panel grounding tabs
- Surface Mount Compatible

Reference Information

Product Specification: PS-44050-003
 Packaging: Tray
 UL File No.: E107635
 CSA File No.: LR19980
 Designed In: Inches

Electrical

Voltage: 125V
 Current: 1.5A
 Dielectric Withstanding Voltage: 1000V AC
 Insulation Resistance: 500 MΩ min.

Mechanical

Durability: 500 cycles min.


Physical

Housing: Black glass-filled, high temperature nylon, UL 94V-0
 Plating: Contact Area—1.27μm (50μ") min. Gold
 Solder Tails—1.27μm (50μ") Tin/Lead on both contact area and solder tails over Nickel overall
 Operating Temperature: -40 to +80°C








44050

High Speed, Right Angle Low Profile Shielded and Unshielded Versions



CATALOG DRAWING (FOR REFERENCE ONLY)



PCB LAYOUT: COMPONENT SIDE
 RECOMMENDED PCB THICKNESS: 1.57/0.062

Modular Plugs and Jacks

0

ORDERING INFORMATION AND DIMENSIONS

Circuits	Loaded Contacts	Order No.				Dimension					
		Unshielded	Shielded		Location F	A	B	C	D	E	F
			With All Panel Grounding Tabs	With Offset Panel Grounding Tabs							
Location E	Location F	Location E	Location F								
8	8	44050-0001				15.24 (.600)	8.89 (.350)	11.43 (.450)	12.83 (.505)		
8	8		44050-0007		44050-0009	15.80 (.622)	8.89 (.350)	11.43 (.450)	13.08 (.515)	3.05 (.120)	
8	8		44050-0002		44050-0004	15.80 (.622)	8.89 (.350)	11.43 (.450)	13.08 (.515)	3.68 (.145)	
8	8		44050-0006		44050-0008	15.80 (.622)	8.89 (.350)	11.43 (.450)	13.08 (.515)	4.57 (.180)	
8	8			44050-0003		44050-0005	15.80 (.622)	8.89 (.350)	11.43 (.450)	13.08 (.515)	3.05 (.120)



PRODUCT SPECIFICATION

CATEGORY 5 RIGHT ANGLE MODULAR JACKS

1.0 SCOPE

This Product Specification covers the 1.27 mm (.050 inch) centerline (pitch) printed circuit board (PCB) modular jack connector series with selective gold and tin-lead plating.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBER(S)

Right Angle, Single Port Modular Jack	44050
Right Angle, Ganged Modular Jack	44150
Right Angle, Stacked Ganged Modular Jack (with light pipes, shielded only)	44170
Right Angle, Stacked Ganged Modular Jack (without light pipes, shielded only)	44520

2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

See the appropriate sales drawings (SD-44050-002, SD-44150-002, SD-44170-001, SD-44520-001) for information on dimensions, materials, plating and markings.

2.3 SAFETY AGENCY APPROVALS

UL File Number.....E107635
CSA File Number.....LR19980

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

FCC Rules and Regulations, Part 68, Subpart F
REA Bulletin 345-81, PE-76; Specification for modular telephone set hardware
ANSI/EIA/TIA-568
IEC-60603-7
UL 1863
MIL-STD-202; General requirements for test specifications

4.0 RATINGS

4.1 VOLTAGE

56.5 V DC
150 V_{RMS} AC (Ringing voltage only)

4.2 CURRENT

1.5 Amps @ 25°C

4.3 TEMPERATURE

Operating: - 40°C to + 70°C

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 1 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25



PRODUCT SPECIFICATION

5.0 PERFORMANCE

5.1 ELECTRICAL REQUIREMENTS

	DESCRIPTION	TEST CONDITION	REQUIREMENT
	Contact Resistance (Low Level)	Mate connectors: apply a maximum voltage of 20 mV and a current of 100 mA . (Measurement locations in Section 7.0)	20 milliohms MAXIMUM [initial]
	Insulation Resistance	Unmated connector, mounted to a PCB: apply a voltage of 100 VDC between adjacent terminals and between terminals to ground.	500 Megohms MINIMUM
	Dielectric Withstanding Voltage	Mate connectors: apply a voltage of 1000 VAC for 1 minute between adjacent terminals and 1500 VAC between terminals to ground.	No breakdown; current leakage < 5 mA
	Capacitance	Measure between adjacent terminals at 1 kHz	10 picofarads MAXIMUM
	Shielding Effectiveness	Measure at frequency from 30 mHz to 400 mHz .	20dB MINIMUM

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 2 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25



PRODUCT SPECIFICATION

5.2 TRANSMISSION PERFORMANCE

ITEM	TEST CONDITION	REQUIREMENT	
	Reference Specification TIA/EIA 568A	Frequency (MHz)	Loss (dB)
5.2.1 Maximum Attenuation	Measurement of signal power loss due to connection made on any pair within the connector under test. Worst result shall be within specification.	1	0.1
		4	0.1
		10	0.1
		16	0.2
		20	0.2
		31.25	0.2
		62.5	0.3
		100	0.4
5.2.2 Minimum Near End Crosstalk	Jack under test shall be terminated with resistor of 100 ohms +/- 1% (see <i>figure 1</i>). Measurements are made in these 2-pair combinations: 1-2, 3-6, 4-5, 7-8. The worst case NEXT loss must be within specification	1	65
		4	65
		10	60
		16	56
		20	54
		25	52
		31.25	50
		62.5	44
5.2.3 Minimum Return Loss	Jack under test shall be terminated with resistor of 100 ohms +/- 1%. (See <i>figure 1</i>) A balanced input signal is applied to a connector pair while signals that are reflected back due to the impedance discontinuities are measured at the same port from which the signal is applied. A measurement shall be done for each pair (1-2, 3-6, 4-5, 7-8).	1	20
		16	20
		20	14
		100	14
		100	14

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 3 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25



PRODUCT SPECIFICATION

5.2 MECHANICAL REQUIREMENTS

	DESCRIPTION	TEST CONDITION	REQUIREMENT
	Connector Mate Force	Mate connector at a rate of 25 ± 6 mm (1 ± ¼ inch) per minute. (Gage dimensions in Section 7.0)	22 N (5 lbf) unshielded MAXIMUM insertion force 35 N (8 lbf) shielded MAXIMUM insertion force
	Durability	Mate connectors up to 500 cycles at a maximum rate of 10 cycles per minute prior to Environmental Tests.	10 milliohms MAXIMUM (change from initial)
	Vibration (Random)	Amplitude: 1.50mm (.060") peak to peak Sweep: 10-55-10 Hz in one minute Duration: 15 minutes ±X,±Y,±Z axis (45 minutes total)	10 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
	Plug Retention Force	Apply an axial pullout force on the plug at a rate of 25 ± 6 mm (1 ± ¼ inch) .	89 N (20 lbf) MINIMUM retention force
	PCB Separation Forces	Apply a perpendicular static load on the plug at a rate of 25 ± 6 mm (1 ± ¼ inch) .	4.5 N (1 lbf) MINIMUM withdrawal force before solder reflow 89 N (20 lbf) MINIMUM withdrawal force after solder reflow
	Shock (Mechanical)	Mate connectors and shock at 50 g's with three saw tooth wave form shocks in the ±X,±Y,±Z axis (18 shocks total).	10 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 4 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL REQUIREMENTS

	DESCRIPTION	TEST CONDITION	REQUIREMENT
	Shock (Thermal)	Mate connectors; expose to 10 cycles of: -40°C to +85°C 30 minutes dwell	10 milliohms MAXIMUM (change from initial) & Visual: No Damage
	Thermal Aging	Mate connectors; expose to: 240 hours at 85±2°C	10 milliohms MAXIMUM (change from initial) & Visual: No Damage
	Humidity (Cyclic)	Mate connectors: expose to 10 cycles at 90-95% relative humidity with temperatures at +25°C and +65°C per MIL-STD-202F method 106F (without -10°C dip)	10 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 200 Megohms MINIMUM & Visual: No Damage
	Solder Resistance	Dip connector terminal tails in solder: Solder Duration: 5±0.5 seconds Solder Temperature: 260±5°C {Recommended same parameters as SMES-152. }	Visual: No Damage to insulator material

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 5 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25




PRODUCT SPECIFICATION

6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage.
See appropriate sales drawings on Sheet 1 for packaging descriptions.

7.0 GAGES AND FIXTURES



TERMINATION RESISTANCE MEASUREMENT POINTS

Connector and plug terminals and wire conductor bulk resistance to be subtracted from measurements







8.0 OTHER INFORMATION

REVISION: B	ECR/ECN INFORMATION: EC No: UCR2002-0992 DATE: 2002/05/22	TITLE: PRODUCT SPECIFICATION CATEGORY 5 RIGHT ANGLE MODULAR JACKS	SHEET No. 6 of 6
DOCUMENT NUMBER: PS-44050-003	CREATED / REVISED BY: MARGULIS 99/10/25	CHECKED BY: ROBERTS 99/10/25	APPROVED BY: ROBERTS 99/10/25


13 12 11 10 9 8 7 6 5 4 3 2 1

J
I
H
G
F
E
D
C
B
A

J
I
H
G
F
E
D
C
B
A




PCB LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: .062/1.57



- NOTES:
 1) MATERIAL:
 HOUSING: NYLON(PA), GLASS FILLED, UL94V-0, COLOR: BLACK
 TERMINALS: PHOSPHOR BRONZE
 2) FINISH:
 TERMINALS:
 SELECT GOLD IN CONTACT AREA: 50 MICROINCHES / 127 MICROMETERS MIN.
 *SELECT TIN IN PC TAIL AREA: 100 MICROINCHES / 2.54 MICROMETERS MIN.
 WITH OVERALL NICKEL UNDERPLATE: 50 MICROINCHES / 127 MICROMETERS MIN.
 *THE PRIMARY SHIPPING CARTON WILL BE LABELED 'COMPLIANT TO ROHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC'. CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD IN THE PC TAILS.
 3) PRODUCT SPECIFICATION AND PROCESSING PARAMETERS: PS-44050-003.
 4) PACKAGING SPECIFICATION:
 CONNECTOR ASSEMBLIES IN THERMOFORMED TRAYS PER MOLEX PACKAGING SPECIFICATION PK-44050-004.
 5) MATES WITH: MODULAR PLUGS THAT CONFORM TO FCC REGULATION PART 68.5.
 6) TERMINAL LENGTHS MAY BE DIFFERENT FROM TERMINAL TO TERMINAL.

CORRECT NOTE #5 FCC NO: UCP2006-2886 DRWNL:LSCHM1DT 2006/06/19 CHKD:LSCHM1DT 2006/06/27 APPR:FSM1TH 2006/06/29	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
		4 PLACES ± --- ± ---	mm INCH	DRAWN BY MARANTO	DATE 98/04/06	CATEGORY 5E MODULAR JACK ASSEMBLIES, SINGLE PORT				
		3 PLACES ± --- ± .010		CHECKED BY ROBERTS	DATE 98/04/06	MOLEX INCORPORATED				
		2 PLACES ± 0.25 ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2°		APPROVED BY ROBERTS	DATE 98/04/06	MATERIAL NO. 440500001	DOCUMENT NO. SD-44050-002	SHEET NO. 1 OF 2		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

12 11 10 9 8 7 6 5 4 3 2 1



ASSEMBLY MATERIAL NUM	DIM -A-	DIM -B-	PANEL GROUND TAB OPTION
440500007	.120/3.05	N/A	ALL
440500002	.145/3.68	N/A	ALL
440500006	.180/4.57	N/A	ALL
440500003	N/A	.120/3.05	ALL
440500009	.120/3.05	N/A	SEE NOTE #6
440500004	.145/3.68	N/A	SEE NOTE #6
440500008	.180/4.57	N/A	SEE NOTE #6
440500005	N/A	.120/3.05	SEE NOTE #6

CORRECT NOTE #5 FCC NO: UCP2006-2886 DR:WALLSCHMIDT 2006/06/19 CHKD:LSCHMIDT 2006/06/27 APPR:FSM TH 2006/06/29 REV:	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2°	DIMENSION STYLE IN/MM DRAWN BY: MARANTO DATE: 98/04/06 CHECKED BY: ROBERTS DATE: 98/04/06 APPROVED BY: ROBERTS DATE: 98/04/06 MATERIAL NO.	SCALE: 4:1 DESIGN UNITS: INCH THIRD ANGLE PROJECTION	CATEGORY 5E MODULAR JACK ASSEMBLIES, SINGLE PORT MOLEX INCORPORATED DOCUMENT NO. SD-44050-002 SHEET NO. 2 OF 2
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE CHART THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		