

| Date | Rev. | Description |
|------|------|-------------|
| | | |
| | | |
| | | |

L01 1.27mm FLAT RIBBON CABLE


UL File No. : E162690
 UL Style : 2651
 Operating Temperature : -20°C to +105°C
 Flammability Rating : UL-VW-1
 Voltage Rating : 300V

Physical

Insulation Material : Polyvinyl Chloride (PVC)
 Conductor : #28AWG (7*0.127) Stranded Tinned Copper
 #26AWG (7*0.16) Stranded Tinned Copper
 Color : Grey With Red Edge

Electrical

Impedance : 115Ω (Unbalanced)
 Capacitance : 12.2 pF/ft.
 Inductance : .14μH/ft.
 Propagation Delay : 1.4 ns/ft.
 Insulation Resistance : 1GΩ/M min.



HOW TO ORDER:

L01 - ¹ - ² - ³ - ⁴ /UNIT - G (RoHS)

| | | | |
|--------------------------------|---------------------------------|---------------------------------------|------------------------------------------------------------------|
| 1.NO. OF CONDUCTOR 06 TO 64 | 2.INSULATION MATERIAL P: PVC | 3.WIRE SIZE A: 28 AWG B: 26 AWG | 4.CABLE LENGTH / UNIT C: CM F: FEET I: INCH M: METER |
|--------------------------------|---------------------------------|---------------------------------------|------------------------------------------------------------------|

| |
|----------------|
| DCC. NO. |
| A4 DRAWING NO. |

| | | | |
|------------------------------------|--------------------------------------|--------|--------------------|
| MATERIAL | GOLDSUN ELECTRONICS CO., LTD. | | |
| JAMECO NO. 644172 | | | |
| DRAWN: Kiki Chen | Description CABLE RIBBON | | Rev. 1 |
| VERIFY PEOPLE: Ada Zheng , Ivy Lan | UNIT: mm | SCALE: | CAS No: ERN No: |
| | SHEET 1 OF 1 | | |