

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 676326

Fast Switching Plastic Rectifier

Major Ratings and Characteristics

$I_{F(AV)}$	1.0 A
V_{RRM}	50 V to 600 V
I_{FSM}	30 A
t_{rr}	200 ns
I_R	5.0 μ A
V_F	1.2 V
T_j max.	150 °C



DO-204AL (DO-41)

Features

- Fast switching for high efficiency
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- Solder Dip 260 °C, 40 seconds



Mechanical Data

Case: DO-204AL, molded epoxy body

Epoxy meets UL-94V-0 Flammability rating

Terminals: Matte tin plated (E3 Suffix) leads, solderable per J-STD-002B and JESD22-B102D

Polarity: Color band denotes cathode end

Typical Applications

For use in fast switching rectification of power supply, inverters, converters and freewheeling diodes for consumer and Telecommunication.

(Note: These devices are not Q101 qualified. Therefore, the devices specified in this datasheet have not been designed for use in automotive or Hi-Rel applications.)

Maximum Ratings

($T_A = 25$ °C unless otherwise noted)

Parameter	Symbol	1N4933	1N4934	1N4935	1N4936	1N4937	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	V
Maximum RMS voltage	V_{RMS}	35	70	145	280	420	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	V
Maximum average forward rectified current 0.375" (9.5 mm) lead length at $T_A = 75$ °C	$I_{F(AV)}$	1.0					A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	30					A
Maximum reverse recovery current ⁽¹⁾	I_{RM}	2.0					A
Operating junction and storage temperature range	T_J, T_{STG}	- 50 to + 150					°C

1N4933 thru 1N4937



Vishay General Semiconductor

Electrical Characteristics

($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)

Parameter	Test condition	Symbol	1N4933	1N4934	1N4935	1N4936	1N4937	Unit
Maximum instantaneous forward voltage	at 1.0 A	V_F	1.2					V
Maximum DC reverse current at rated DC blocking voltage	$T_A = 25\text{ }^\circ\text{C}$ $T_A = 100\text{ }^\circ\text{C}$	I_R	5.0 100					μA
Maximum reverse recovery time	$I_F = 1.0\text{ A}$, $V_R = 30\text{ V}$, $di/dt = 50\text{ A}/\mu\text{s}$, $I_{rr} = 10\% I_{RM}$	t_{rr}	200					ns
Typical junction capacitance	at 4.0 V, 1 MHz	C_J	12					pF

Thermal Characteristics

($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	1N4933	1N4934	1N4935	1N4936	1N4937	Unit
Typical thermal resistance ⁽¹⁾	$R_{\theta JA}$ $R_{\theta JL}$	55 25					$^\circ\text{C}/\text{W}$

Note:

(1) Thermal resistance from junction to ambient, and from junction to lead at 0.375" (9.5 mm) lead length, P.C.B. mounted

Ratings and Characteristics Curves

($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)




Figure 1. Forward Current Derating Curves




Figure 2. Maximum Non-repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance




Figure 4. Typical Reverse Characteristics





Figure 6. Typical Transient Thermal Impedance

Package outline dimensions in inches (millimeters)



NOTE: Lead diameter is 0.026 (0.66) for suffix "E" part numbers
0.023 (0.58)