

AC-to-DC Regulated Wall Adapters

Energy Star Worldwide Interchangeable AC-to-DC Regulated Switching Wall Adapters

Meets US and European Energy Star compliance. Approved for European high-efficiency power applications.

- Field changeable AC Plug Clips (sold separately, see below)
- Regulated output • Double insulated
- Input voltage: 90-264VAC @ 47-63Hz • Power-On LED
- Output connector: 2.1mm x 5.5mm female center positive; except P/N 2144809: 2.5mm x 5.5mm female straight center positive
- Load regulation: ±5% • Class B EMI • Color: black
- Applications: wireless communications, portable equipment, digital camera, peripherals and networking



* Web Code: NBH



Phihong & Mean Well AC Plug Clips (below)

NEW MARKED IN PINK



Shown w/o AC Plug Clip
AC Plug Clips Not Included

Wall Adapters (AC Plug Clip required, not included)

Part No.	Manufacturer	Mfr. Part No.	Output Volt. (VDC)	Current (A)	Power (W)	Ripple (mVp-p)	Line Regulation	Efficiency (%)	Dimensions (L" x W" x H")	Pricing		
										1	5	25
2144809	Phihong	PSA08R-050†#	5	1.0	5	50	±1%	70	2.8 x 1.8 x 1.0	\$10.95	\$9.95	\$8.95
2139815	Phihong	PSAC05R-050(P)Ⓢ	5	1.0	5	50	±1%	60 - 75	2.8 x 1.8 x 1.2	11.95	10.95	9.95
2158240	Phihong	PSM11R-050##	5	2.0	10	100	±5%	70	2.8 x 1.7 x 1.2	10.95	9.95	8.95
2082302	Mean Well	GE12I05-P1JⓈ	5	2.0	10	50	±5%	70	2.8 x 1.6 x 1.5	11.95	10.95	9.95
2155401	Phihong	PSA15R-090P-RⓈ	9	1.66	15	90	±5%	75	2.8 x 2.0 x 1.3	15.95	14.95	13.95
2082311	Mean Well	GE18I09-P1JⓈ	9	2.0	18	100	±5%	75	3.2 x 1.7 x 1.6	17.95	16.95	14.49
2138951	Phihong	PSA11R-120	12	0.83	10	120	±1%	65	2.8 x 1.8 x 1.2	9.95	8.95	7.95
2108656	Phihong	PSC12R-120Ⓢ	12	1.0	12	240	±5%	78	2.8 x 1.8 x 1.2	14.95	13.95	12.95
2154986	ReliaPro	FW75550/12Ⓢ*	12	1.25	15	150	±5%	80	3.5 x 2.0 x 1.3	16.95	15.95	14.95
2100179	Phihong	PSAA20R-120Ⓢ	12	1.67	20	120	±5%	81	2.8 x 2.0 x 1.3	17.95	16.95	14.49
2082337	Mean Well	GE12I15-P1JⓈ	15	0.8	12	150	±3%	76	2.8 x 1.6 x 1.5	13.95	12.49	10.95
2082345	Mean Well	GE12I24-P1JⓈ	24	0.63	15	240	±3%	80	2.8 x 1.6 x 1.5	14.95	13.95	12.95
2155410	Phihong	PSC30R-240-RⓈ	24	1.25	30	240	±1%	80	3.9 x 2.5 x 1.4	17.95	16.49	14.95

† Comes with USA AC plug clip (RPA) # 2.5mm x 5.5mm female plug ## Mini USB plug * Kit includes US, UK, EU, AUS plugs

Phihong AC Plug Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	250
229155	RPAⓈ	USA AC plug only	\$1.25	\$1.19	\$1.09	\$0.99
229163	RPEⓈ	European AC plug only	1.25	1.19	1.09	.99
229181	RPKITⓈ	Kit includes RPA/RPE/RPK/RPS clips (4)	4.49	4.25	3.95	3.59

Mean Well AC Plug Clips (sold separately, required for above adapters)

Part No.	Mfr. P/N	Description (see above for photos)	1	10	50	250
2082353	AC-Plug-USⓈ	USA AC plug only	\$1.25	\$1.19	\$1.09	\$0.99
2082361	AC-Plug-EUⓈ	European AC plug only	1.25	1.19	1.09	.99
2082396	AC-Plug-MIXⓈ	Kit includes US, EU, UK & AU clips (4)	4.49	4.25	3.95	3.59



AC-to-DC Regulated Linear Wall Adapters

* Web Code: WAZ

We specialize in Wall Adapters - Call for additional OEM PRICING.

◆ Polarity figures & photos on next page

Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ◆	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Voltage (VDC)	Current (mA)								1	10	50	250
164101	ReliaPro	GPU410500500WD00	5	500	2.1mm x 5.5mm F 2	120 @ 60	3.1 x 2.1 x 1.7	Black	6'	0.6	UL/CUL	\$10.95	\$9.95	\$8.95	\$7.95
319986	ReliaPro	DV-580R	5	800	2.5mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 2.0	Black	6'	1.0	UL/CUL	8.95	7.95	6.95	5.95
2081609	Condor	RWP480505	5	1000	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	8.95	7.95	6.95	5.95
1953612	ReliaProⓈ	DBU0501000	5	1000	2.1mm x 5.5mm F 2	120 @ 60	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	9.95	8.95	7.95	7.49
168605	ReliaPro	DBU0501000	5	1000	2.5mm x 5.5mm F 2	120 @ 60	3.3 x 2.2 x 1.9	Black	6'	1.2	UL/CSA	10.95	9.95	8.95	7.95
190512	ReliaPro	DBU60020-H3570	6	200	2.1mm x 5.5mm F 2	120 @ 60	2.2 x 1.7 x 1.5	Black	6'	0.4	UL/CUL	9.95	8.95	7.95	6.95
2138716	ReliaPro	D41-06-500R	6	500	2.1mm x 5.5mm F 1	120 @ 60	2.6 x 2.1 x 1.5	Black	6'	0.6	UL/CUL	8.95	7.95	6.95	5.95
283573	ReliaPro	ADR-6V500MA-2.1	6	500	2.1mm x 5.5mm F 2	120 @ 60	3.1 x 2.0 x 1.7	Black	6'	0.6	UL/CSA	10.95	9.95	8.95	7.95
1953701	ReliaPro	ADR-6V500MA-2.5	6	500	2.5mm x 5.5mm F 2	120 @ 60	3.1 x 2.0 x 1.7	Black	6'	0.6	UL/CSA	7.95	6.95	5.95	5.49
1953719	ReliaPro	DBU0601000	6	1000	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.3 x 2.0	Black	6'	1.3	UL/CSA	12.95	11.49	9.95	8.95
190529	ReliaPro	AD9123	9	250	2.5mm x 5.5mm right angle F 2	120 @ 60	2.5 x 2.0 x 1.6	Black	6'	0.5	UL/CSA	10.95	9.95	8.95	7.95
1953639	ReliaProⓈ	DCU09050	9	500	2.1mm x 5.5mm F 2	120 @ 60	2.4 x 2.0 x 1.6	Black	6'	0.9	UL/CSA	10.95	10.49	9.95	8.95
1953647	ReliaProⓈ	SF41-0900500RU	9	500	2.5mm x 5.5mm F 2	120 @ 60	3.0 x 2.0 x 1.6	Black	6'	0.9	UL/CSA	10.95	10.49	9.95	8.95
220898	ReliaPro	DCU120020	12	200	2.1mm x 5.5mm F 1	120 @ 60	2.5 x 2.0 x 1.7	Black	6'	0.5	UL/CUL	8.95	7.95	6.95	6.25
162996	ReliaPro	DDU120050	12	500	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.2 x 1.9	Black	6'	0.9	UL/CUL	11.95	10.95	9.95	8.95
170245	ReliaPro	RDU120100	12	1000	2.1mm x 5.5mm F 2	120 @ 60	3.2 x 2.3 x 2.0	Black	6'	1.2	UL/CUL	14.95	13.49	11.95	10.95
1953663	ReliaProⓈ	DCU1201000	12	1000	2.5mm x 5.5mm F 2	120 @ 60	3.3 x 2.3 x 2.0	Black	6'	1.2	UL/CSA	14.95	13.49	11.95	10.95
174861	ReliaPro	DFU240050	24	500	2.1mm x 5.5mm F 2	120 @ 60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95
174879	ReliaPro	DCU090025	24	500	2.5mm x 5.5mm F 2	120 @ 60	3.4 x 2.7 x 2.2	Black	6'	1.3	UL/CUL	14.95	13.49	11.95	10.95

More AC-to-DC Wall Adapters listed on pages 101-102 & 104-105

BEST SELLING - LINEAR REGULATED/UNREGULATED WALL ADAPTERS

P/N 164101 5V @ 0.5A \$10.95 (above)
 P/N 283573 6V @ 0.5A 10.95 (above)
 P/N 170245 12V @ 1A 14.95 (above)



P/N 100175 9V @ 0.6A \$7.95 (pg 104)
 P/N 102496 12V @ 0.5A 7.95 (pg 105)
 P/N 100870 12V @ 1A 9.95 (pg 105)

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone at 1-800-831-4242 or Online at www.Jameco.com