


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 683171



Sockets

DIP Sockets

AMP 1-390261-9 Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 1-390261-9)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<input type="checkbox"/> General Info <input type="checkbox"/> Sales Info <input type="checkbox"/> Assembly Subcontractors	<input type="checkbox"/> Pricing <input type="checkbox"/> Product Availability	<input type="checkbox"/> Tooling

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Wave solder capable to 240°C, Wave solder capable to 265°C, Not reviewed for lead free solder process
Product Type:	DIP Socket
No. of Positions:	28
Row-to-Row Spacing (mm [in]):	7.62 [0.300]
Contact Mount:	Thru Hole
Mount Style:	Vertical
Centerline (mm [in]):	2.54 [0.100]

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Insulation Resistance (MΩ):	10,000
Contact Resistance (mΩ):	30

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

Profile:	Standard
Frame Style:	Ladder
Leg Style:	Straight
Contact Material:	Phosphor Bronze
Contact Mating Area Plating:	Tin
Contact Style:	Stamped + Formed
Mating Contact Type:	Dual Leaf
Height Above PC Board (mm [in]):	5.10 [0.200]
Temperature Range (°C):	-40 – +105
Packaging Method:	Tube
Termination Post Length (mm [in]):	3.00 [0.118]
PCB Mount Angle:	Horizontal

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

