

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
120 X 120 X 25	AD1224HS-A71GL	S	24	0.24	5.76	2200	85.2	0.136	39.1	156	1	UL,CUL,TUV,CE	90	30.80
120 X 120 X 25	AD1224HS-A73GL	S	24	0.24	5.76	2200	85.2	0.136	39.1	156	3	CE	90	30.80
120 X 120 X 25	AD1224US-A71GL	S	24	0.25	6.00	2500	98.6	0.176	43.3	156	1	CE	90	30.80
120 X 120 X 25	AD1248HB-A71GL	BALL	48	0.25	9.60	2200	85.2	0.136	39.1	156	1	CE	90	30.80
120 X 120 X 32	AD2512LX	HYPRO	12	0.15	1.80	1200	12.0	0.109	34.3	276	0	TUV,CE		
120 X 120 X 32	AD2512MX	HYPRO	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	UL,CUL,CE		
120 X 120 X 32	AD2512LB	BALL	12	0.15	1.80	1200	12.0	0.109	34.3	276	0,3	TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	UL,CUL,TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	2	TUV,CE		
120 X 120 X 32	AD2512MB	BALL	12	0.60	7.20	2300	23.7	0.621	51.1	276	3	CE		
120 X 120 X 32	AD2512HB	BALL	12	0.65	7.80	2500	25.2	0.640	51.0	276	0,3	CE		
120 X 120 X 32	AD2512UB	BALL	12	1.00	8.00	3200	33.1	1.121	55.8	276	0,2,3	CE		
120 X 120 X 32	AD2512LS	S	12	0.15	1.80	1200	12.0	0.109	34.3	276	0	TUV,CE		
120 X 120 X 32	AD2512MS	S	12	0.60	7.20	2300	23.7	0.621	51.1	276	0	TUV,CE		
120 X 120 X 32	AD2512HS	S	12	0.65	7.80	2500	25.2	0.640	51.0	276	0	CE		
120 X 120 X 32	AD2512US	S	12	1.00	8.00	3200	33.1	1.121	55.8	276	0	CE		
120 X 120 X 32	AD2524MX	HYPRO	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,TUV,CE		
120 X 120 X 32	AD2524MB	BALL	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,CUL,CSA,TUV,CE		
120 X 120 X 32	AD2524HB	BALL	24	0.43	9.80	2500	25.2	0.640	51.0	276	0	CE		
120 X 120 X 32	AD2524UB	BALL	24	0.50	9.80	2800	29.4	0.800	52.5	276	0	CE		
120 X 120 X 32	AD2524MS	S	24	0.40	9.60	2300	23.7	0.621	51.1	276	0	UL,CSA,TUV,CE		
120 X 120 X 32	AD2524US	S	24	0.50	9.80	2800	29.4	0.800	52.5	276	0	CE		
120 X 120 X 38	AD1212LX-F51	HYPRO	12	0.24	2.88	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212LX-F53	HYPRO	12	0.24	2.88	1950	72.3	0.135	32.9	297	3	CE	40	33.66
120 X 120 X 38	AD1212MX-F51	HYPRO	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,CSA,CE	40	33.66
120 X 120 X 38	AD1212MX-F53	HYPRO	12	0.35	4.20	2540	94.0	0.244	41.0	297	3	CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-F51	HYPRO	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,4	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-F52	HYPRO	12	0.50	6.00	2800	104.8	0.270	42.8	297	2	CSA,CE	40	33.66
120 X 120 X 38	AD1212HX-Y51	HYPRO	12	0.40	4.80	2750	108.0	0.215	43.3	213	1	CE	40	33.66
120 X 120 X 38	AD1212LB-F51	BALL	12	0.24	2.88	1950	72.3	0.135	32.9	297	1,3	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212LB-F52	BALL	12	0.24	2.88	1950	72.3	0.135	32.9	297	2	UL,CE	40	33.66
120 X 120 X 38	AD1212MB-F51	BALL	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MB-F52	BALL	12	0.35	4.20	2540	94.0	0.244	41.0	297	2,3,4,7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-F51	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,3	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-F52	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	2,4	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212HB-F57	BALL	12	0.50	6.00	2800	104.8	0.270	42.8	297	7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HB-Y51	BALL	12	0.40	4.80	2750	108.0	0.215	43.3	213	1,3	CE	40	33.66
120 X 120 X 38	AD1212UB-F51	BALL	12	0.07	0.84	3200	122.0	0.394	48.0	297	1,2,4	CE	40	33.66
120 X 120 X 38	AD1212UB-F53	BALL	12	0.07	0.84	3200	122.0	0.394	48.0	297	3	UL,CUL,CE	40	33.66
120 X 120 X 38	AD1212LS-F51	S	12	0.24	2.88	1950	72.3	0.135	32.9	297	1	UL,CUL,TUV,CE	40	33.66
120 X 120 X 38	AD1212MS-F51	S	12	0.35	4.20	2540	94.0	0.244	41.0	297	1	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MS-F52	S	12	0.35	4.20	2540	94.0	0.244	41.0	297	2,3,4,7	CSA,CE	40	33.66
120 X 120 X 38	AD1212HS-F51	S	12	0.50	6.00	2800	104.8	0.270	42.8	297	1,4	UL,CUL,TUV,CSA,CE	40	33.66

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED