

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

Jameco Part Number 693329

**MODEL : RS-100-48**

**OUTPUT FUNCTION TEST**

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	RIPPLE & NOISE	V1: 200 mVp-p (Max)	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	V1: 89 mVp-p (Max)	P
2	OUTPUT VOLTAGE ADJUST RANGE	CH1: 45.6V~ 52.8 V	I/P: 230 VAC I/P: 115 VAC O/P:MIN LOAD Ta:25°C	43.2V~ 54 V/ 230VAC 43.2V~ 54 V/ 115VAC	P
3	OUTPUT VOLTAGE TOLERANCE	V1: -1 %~ 1% (Max)	I/P: 100 VAC / 264 VAC O/P:FULL/ 0 % LOAD Ta:25°C	V1: 0.05 %~ -0.05 %	P
4	LINE REGULATION	V1:-0.5 %~ 0.5 % (Max)	I/P: 100 VAC ~ 264 VAC O/P:FULL LOAD Ta:25°C	V1: 0.05 %~ -0.05 %	P
5	LOAD REGULATION	V1: -0.5 %~0.5 % (Max)	I/P:230 VAC O/P:FULL ~MIN LOAD Ta:25°C	V1: 0.05 %~ -0.05 %	P
6	SET UP TIME	230 VAC/500 ms (Max) 115 VAC/1200 ms (Max)	I/P:230 VAC I/P:115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 172 ms 115VAC/ 160 ms	P
7	RISE TIME	230 VAC/20 ms (Max) 115 VAC/30 ms (Max)	I/P:230 VAC I/P:115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 9 ms 115VAC/ 10 ms	P
8	HOLD UP TIME	230 VAC/ 50 ms (TYP) 115 VAC/ 10 ms (TYP)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 99 ms 115VAC/ 18 ms	P
9	OVER/UNDERSHOOT TEST	< ±5%	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	TEST: <5 %	P
10	DYNAMIC LOAD	V1: 4800 mVp-p	I/P: 230 VAC O/P:FULL /Min LOAD 90%DUTY/1KHZ Ta:25°C	463 mVp-p	P

**INPUT FUNCTION TEST**

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	INPUT VOLTAGE RANGE	88VAC~ 264 VAC	I/P:TESTING O/P:FULL LOAD Ta:25°C	70 V~ 264 V	P
			I/P: LOW-LINE-3V= 85 V HIGH-LINE+15%= 300 V O/P:FULL/MIN LOAD ON: 30 Sec . OFF: 30 Sec 10MIN ( AC POWER ON/OFF NO DAMAGE )	TEST: OK	
2	INPUT FREQUENCY RANGE	47 HZ ~ 63 HZ NO DAMAGE OSC	I/P: 88 VAC ~ 264 VAC O/P:FULL-MIN LOAD Ta:25°C	TEST: OK	P
3	EFFICIENCY	84 % (TYP)	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	84.3%	P
4	INPUT CURRENT	230 V/ 1.5 A(TYP) 115 V/ 2.5 A (TYP)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	I = 1.3 A/ 230 VAC I = 2 A/ 115 VAC	P
5	INRUSH CURRENT	230 V/ 40 A (TYP) COLD START	I/P:230 VAC O/P:FULL LOAD Ta:25°C	I = 33 A/ 230 VAC	P
6	LEAKAGE CURRENT	< 2 mA / 240 VAC	I/P:254 VAC O/P:Min LOAD Ta:25°C	L-FG: 0.5 mA N-FG: 0.5 mA	P

**PROTECTION FUNCTION TEST**

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	OVER LOAD PROTECTION	110 %~ 150 %	I/P: 230 VAC I/P: 115 VAC O/P: TESTING Ta:25°C	125 %/ 230 VAC 124 %/ 115 VAC Hiccup Mode	P
2	OVER VOLTAGE PROTECTION	CH1: 55.2 V~ 64.8	I/P: 230 VAC I/P: 115 VAC O/P: MIN LOAD Ta:25°C	63 V/ 230 VAC 63 V/ 115 VAC Hiccup Model	P
3	SHORT PROTECTION	SHORT EVERY OUTPUT 1 HOUR NO DAMAGE	I/P: 264 VAC O/P: Full LOAD Ta:25°C	NO DAMAGE Hiccup Mode	P



**SAFETY TEST**

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	WITHSTAND VOLTAGE	I/P-O/P: 3 KVAC/min I/P-FG: 1.5 KVAC/min O/P-FG: 0.5 KVAC/min	I/P-O/P: 3.6 KVAC/min I/P-FG: 1.8 KVAC/min O/P-FG: 0.6 KVAC/min Ta:25°C	I/P-O/P: 4.92 mA I/P-FG: 4.59 mA O/P-FG: 2.46 mA NO DAMAGE	P
2	ISOLATION RESISTANCE	I/P-O/P:500VDC>100MΩ I/P-FG: 500VDC>100MΩ O/P-FG:500VDC>100MΩ	I/P-O/P: 500 VDC I/P-FG: 500 VDC O/P-FG: 500 VDC Ta:25°C	I/P-O/P: 9G Ω I/P-FG: 6 G Ω O/P-FG: 15 G Ω NO DAMAGE	P
3	GROUNDING CONTINUITY	FG(PE) TO CHASSIS OR TRACE < 100 mΩ	40 A / 2min Ta:25°C	4 mΩ	P
4	APPROVAL	TUV: Certificate NO : R50045826 UL: File NO : E183223			P

**E.M.C TEST**

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	HARMONIC	EN61000-3-2 CLASS A	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	PASS	P
2	CONDUCTION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL/50% LOAD Ta:25°C	PASS Test by certified Lab	P
3	RADIATION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL LOAD Ta:25°C	PASS Test by certified Lab	P
4	E.S.D	EN61000-4-2 INDUSTRY AIR:8KV / Contact:4KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
5	E.F.T	EN61000-4-4 INDUSTRY INPUT: 2KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
6	SURGE	IEC61000-4-5 INDUSTRY L-N :2KV L,N-PE:4KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
7	Test by certified Lab & Test Report Prepare				



## M.T.B.F &amp; LIFE CYCLE CALCULATION

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	CAPACITOR LIFE CYCLE	SUPPOSE C 64 IS THE MOST CRITICAL COMPONENT I/P: 230 VAC O/P:FULL LOAD Ta= 25 °C LIFE TIME= 123687 HRS I/P: 230 VAC O/P:FULL LOAD Ta= 50 °C LIFE TIME= 27838 HRS			P
2	MTBF	MIL-HDBK-217F NOTICES2 PARTS COUNT TOTAL FAILURE RATE: 260.8K HRS			P

## COMPONENT STRESS TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	Power Transistor (D to S) or (C to E) <b>Peak Voltage</b>	Q1 Rated 2SK2082 :800 V/9 A	I/P:High-Line +3V =267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 408 V (2) 568 V (3) 700 V	P
2	Diode <b>Peak Voltage</b>	D61 Rated FCF16A6B : 600 V/ 16	I/P:High-Line +3V =267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 466 V (2) 548 V (3) 518 V	P
3	Clamp Diode <b>Peak Voltage</b>	D1 Rated HER208: 1K V/2 A	I/P:High-Line +3V =267 V O/P: (1)Full Load (2) Dynamic Load 90%Duty/1KHz Ta:25°C	(1) 562 V (2) 504 V	P
4	<b>Input Capacitor Voltage</b>	C 5 Rated :150u / 400 V	I/P:High-Line +3V =267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25°C	(1) 390 V (2) 370 V (3) 370 V	P
5	<b>Control IC Voltage Test</b>	U 1 Rated 1203 : 16 V	I/P:High-Line +3V =267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25°C	(1) 14.6 V (2) 14.6 V (3) 14.1 V	P

DATE	SAMPLE	TEST RESULT	TESTER	APPROVAL
2004/1/19	RD SMAPLE	PASS	VICENT TSENG	MAX LIN
2004/7/7	PRODUCT SAMPLE A404B33	PASS	VICENT TSENG	MAX LIN
2004/8/16	PRODUCT SAMPLE A407C27	PASS	VICENT TSENG	MAX LIN

2003/12/12 A50-F023