



[Click Here to Request a Large Quantity Quote](#)

[AC-to-DC Regulated Linear Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Input Voltage (VAC)	Input Frequency	Family	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
1953612	Jameco Reliapro	DDU050100M2270	5	1	5	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$10.95
168605	Jameco Reliapro	DDU050100H4660	5	1	5	120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL, CUL	\$10.95
2289151	Arndt	FE4823-050E120	5	1.2	6	120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL, CUL	\$11.95
2289175	Arndt	WK-102	6	0.75	4.5	120	60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	UL	\$9.95
1953639	Jameco Reliapro	GPU41090500WD00	9	0.5	4.5	120	50Hz to 60Hz	GPU	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$10.95
1953647	Jameco Reliapro	GPU410900500WDOO	9	0.5	4.5	120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL, CUL	\$10.95
220898	Jameco Reliapro	DCU120020G2420	12	0.2	2.4	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	UL, CUL	\$7.95
2236789	Jameco Reliapro	DCU120020-G2421	12	0.2	2.4	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$6.95
162996	Jameco Reliapro	DDU120050F0980	12	0.5	6	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$12.95
170245	Jameco Reliapro	DDU120100H4480	12	1	12	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$14.95
1953663	Jameco Reliapro	DDU120100M2250	12	1	12	120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL, CUL	\$14.95
2289119	Arndt	JOD-48U-35	15	1	15	120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL, CUL	\$10.95
2279343	Jameco Reliapro	DCV240015RV0210	24	0.15	3.6	230	50 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	CE	\$10.95
174879	Jameco Reliapro	DFU240050F1121	24	0.5	12	120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL, CUL	\$13.95

