



[Click Here to Request a Large Quantity Quote](#)

Standard Output 5mm LEDs

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Brightness (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Lead Pitch	Price 1	Price 10
138691	Jameco Valuepro	LVB3330	5mm, T-1 3/4	Blue	10	Diffused	36	5.5	30 mA	430 nm	8.6	0.1"	\$0.99	\$0.89
693901	MCD Electronics	MCDL-5013GD	5mm, T-1 3/4	Green	12.5	Diffused	60	2.1	10 mA	565 nm	8.6	0.1"	\$0.25	\$0.10
697653	Lite-On Electronics	LTL-4233	5mm, T-1 3/4	Green	19	Diffused	36	2.6	30 mA	569 nm	8.6	0.1"	\$0.25	\$0.12
697531	Lite-On Electronics	LTL-307G	5mm, T-1 3/4	Green	19	Diffused	50	2.6	30 mA	569 nm	8.6	0.1"	\$0.25	\$0.15
334086	Jameco Valuepro	LG13740	5mm, T-1 3/4	Green	20	Diffused	68	2.6	30 mA	565 nm	8.6	0.1"	\$0.25	\$0.10
1870593	Everlight Electronics	MV64530	5mm, T-1 3/4	Green	20	Diffused	75	2.2	20 mA	562 nm	8.6	0.1"	\$0.39	\$0.29
2279199	Jameco Valuepro	5WLG3330	5mm, T-1 3/4	Green	25	Diffused	30	1.7	20 mA	565 nm	8.6	0.1"	\$0.25	\$0.15
790217	Lite-On Electronics	LTL-307GE	5mm, T-1 3/4	Green	29	Non Diffused	40	2	30 mA	565 nm	8.6	0.2"	\$0.25	\$0.10
34761	Jameco Valuepro	LG3330	5mm, T-1 3/4	Green	30	Diffused	36	2.6	30 mA	565 nm	8.6	0.1"	\$0.25	\$0.15
2186259	Lite-On Electronics	LTL-5238	5mm, T-1 3/4	Green	34	Water Clear	44	2.1	20 mA	565 nm	6.05	0.1"	\$0.25	\$0.15
2230547	Sunled Corporation	XLUG53C	5mm, T-1 3/4	Green	79	Non Diffused	20	2.0	10 mA	565 nm	8.6	0.1"	\$0.25	\$0.12
2193897	Huey Jann Electronics	HB5-133	5mm, T-1 3/4	Green	80	Diffused	30	2.15	25 mA	570 nm	8.7	0.1"	\$0.25	\$0.06
302033	Jameco Valuepro	LT1814-81	5mm, T-1 3/4	Orange	10	Non Diffused	10	2.1	30 mA	650 nm	8.7	0.1"	\$0.25	\$0.10
152857	Jameco Valuepro	LT1841R81-R	5mm, T-1 3/4	Orange	23.1	Diffused	45	2.4	20 mA	630 nm	8.7	0.1"	\$0.25	\$0.08
107393	Jameco Valuepro	LE3330	5mm, T-1 3/4	Orange	24	Diffused	36	2.6	30 mA	635 nm	8.6	0.1"	\$0.25	\$0.12

Jameco Part #	Manufacturer	Manufacturer Part #	Package	Color	Brightness (mcd)	Lens Type	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Wavelength	Height (mm)	Lead Pitch	Price 1	Price 10
2155268	Jameco Valuepro	BVL-501E1D	5mm, T-1 3/4	Orange	750	Diffused	25	2.1	30 mA	622 nm	8.6	0.1"	\$0.25	\$0.08
210825	BV Optotech	BVU-5M1QN1	5mm, T-1 3/4	Orange Red	600	Diffused	30	2.1	20 mA	615 nm	8.6	0.1"	\$0.25	\$0.10
94511	Jameco Valuepro	LH3330	5mm, T-1 3/4	Red	4.5	Diffused	36	2.6	15 mA	697 nm	8.6	0.1"	\$0.25	\$0.15
253753	Major Brands	HLMP-3301	5mm, T-1 3/4	Red	7	Diffused	65	3.0	30 mA	635 nm	8.89	0.1"	\$0.25	\$0.22
2006730	Lite-On Electronics	LTL-307E-3	5mm, T-1 3/4	Red	12.6	Diffused	40	2.6	30 mA	623 nm	8.7	0.1"	\$0.25	\$0.15
2193900	Lite-On Electronics	LTL-307UR-002	5mm, T-1 3/4	Red	12.6	Diffused	50	1.8	40 mA	470 nm	8.3	0.1"	\$0.25	\$0.15
697602	Lite-On Electronics	LTL-4223	5mm, T-1 3/4	Red	19	Diffused	36	2.6	30 mA	623 nm	8.6	0.1"	\$0.25	\$0.06
697522	Lite-On Electronics	LTL-307E-002A	5mm, T-1 3/4	Red	19	Diffused	50	2.6	30 mA	623 nm	8.6	0.1"	\$0.25	\$0.12
790081	Lite-On Electronics	LTL-10223W	5mm, T-1 3/4	Red	60	Diffused	60	2.6	30 mA	623 nm	8.6	0.1"	\$0.25	\$0.12
333973	Jameco Valuepro	UT1871-81-M1-R	5mm, T-1 3/4	Red	75	Diffused	36	2.2	30 mA	643 nm	8.6	0.1"	\$0.25	\$0.12
2295879	Jameco Valuepro	PL16-CTR12	5mm, T-1 3/4	Red Orange	190	Diffused	10	2.1	20 mA	635 nm	8.6	0.1"	\$0.25	\$0.15
34825	Jameco Valuepro	LY3330	5mm, T-1 3/4	Yellow	12	Diffused	36	2.8	20 mA	585 nm	8.6	0.1"	\$0.25	\$0.15
697696	Lite-On Electronics	LTL-4253	5mm, T-1 3/4	Yellow	19	Diffused	36	2.6	20 mA	588 nm	8.6	0.1"	\$0.25	\$0.05
697549	Lite-On Electronics	LTL-307Y	5mm, T-1 3/4	Yellow	29	Diffused	50	2.6	20 mA	588 nm	8.6	0.1"	\$0.25	\$0.09
2121666	Lite-On Electronics	LTL-307YE-081	5mm, T-1 3/4	Yellow	40	Non Diffused	40	2.1	20 mA	588 nm	8.6	0.1"	\$0.25	\$0.15
2193985	Arndt	MYB51D	5mm, T-1 3/4	Yellow	55	Diffused	70	2.6	20 mA	585 nm	0.87	0.1"	\$0.25	\$0.08
334108	Jameco Valuepro	UT1831-81-R	5mm, T-1 3/4	Yellow	90	Non Diffused	10	2.6	30 mA	590 nm	8.6	0.1"	\$0.25	\$0.12
2276831	Major Brands	HLMP-3850	5mm, T-1 3/4	Yellow	140	Water Clear	24	2.1	30 mA	583 nm	9.19	0.1"	\$0.45	\$0.39