

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**


The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 839148

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00	J	REVISED PER 0G3B-0960-04	22-NOV-04	KW CJ

- 1. 150°C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION ONLY. MAXIMUM OPERATING TEMPERATURE REMAINS 105°C.
- 2. INDIVIDUAL CORING FEATURES AROUND BASES OF SILOS MAY NOT BE PRESENT IN ALL LOCATIONS SHOWN.



HIGH TEMP NYLON, UL94V-2, BLACK	1-770581-0
NYLON, UL94V-0, WHITE	770581-1
MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER	12-MAY-2004	Tyco Electronics Corporation Harrisburg, Pa 17105-3608															
DIMENSIONS: mm [INCHES]		CHK C. JONES	12-MAY-2004	NAME															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES	12-MAY-2004	PRODUCT SPEC															
<table border="0"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>± 0.13 [.005]</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td></td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	± 0.13 [.005]	4 PLC	±	ANGLES	±	FINISH		APPLICATION SPEC		PLUG, 12 CIRCUIT, MINI UNIVERSAL MATE-N-LOK™	
0 PLC	±																		
1 PLC	±																		
2 PLC	±																		
3 PLC	± 0.13 [.005]																		
4 PLC	±																		
ANGLES	±																		
FINISH																			
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO G-770581														
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV J														

**METRIC**