

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 841053

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19  
 BY AMP INCORPORATED. ALL RIGHTS RESERVED.  
 © COPYRIGHT 19

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
B		REVISED(ECR-05-014095)		11OCT05	B.W.	S.Y.	

PC BOARD MOUNTING DIMENSIONS 4

1 MATERIAL:  
SHELL & CONTACTS: COPPER ALLOY.  
HOUSING: UL 94V-0 RATED, THERMOPLASTIC, BLACK.

2 PLATING:  
CONTACTS: 0.076μm MINIMUM GOLD OVER 0.76μm MINIMUM PALLADIUM-NICKEL ON MATING AREA.  
3.8μm MINIMUM MATTE TIN ON SOLDER TAILS.  
BOTH OVER 1.27μm MINIMUM NICKEL.  
CONTACT ALTERNATE PLATING: 0.76μm MIN GOLD ON MATING AREA, 3.8μm MIN MATTE TIN ON SOLDER TAILS, BOTH OVER 1.27μm MIN NICKEL.  
SHELL: 2.0~5.0μm MINIMUM TIN.

3 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

5 PLATING:  
CONTACTS: 0.76μm MINIMUM GOLD ON MATING AREA, 3.8μm MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER 1.27μm MINIMUM NICKEL.  
SHELL: 2.0~5.0μm MINIMUM TIN.

6 PLATING:  
CONTACTS: 0.38μm MINIMUM GOLD ON MATING AREA, 3.8μm MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER 1.27μm MINIMUM NICKEL.  
SHELL: 2.0~5.0μm MINIMUM TIN.

7 RECOMMEND:  
MATING FORCE: 35N MAX.  
UNMATING FORCE: 13N MIN.  
RECOMMENDED MATING PLUG SHOULD MEET USB2.0 STANDARD.

SECTION X-X

6	NO	BLACK	292304-5
5	NO	BLACK	292304-4
2	YES	BLACK	292304-3
2	YES	NATURAL	292304-2
2	NO	BLACK	292304-1
PLATING	HIGH TEMPERATURE COMPATIBLE	HOUSING COLOR	PART NUMBER

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN J.JIANG 23FEB04		Tyco electronics coporation Shanghai, P.R.China, 200233	
DIMENSIONS: mm		CHK S.YAO 23FEB04		NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 4 POSITION, THRU-HOLE, TYPE B UNIVERSAL SERIAL BUS, LEAD FREE VERSION	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD T.SASAKI 23FEB04	SIZE A2	CAGE CODE 00779	DRAWING NO C=292304
MATERIAL		PRODUCT SPEC	WEIGHT	SCALE 5:1	SHEET 1 OF 1
1		2	CUSTOMER DRAWING		

AMP 1471-9 REV 10/93 Translated 040217.101735 (YYMMDD.HHMMSS) from Computervision, Inc., Medusa Revision 12.2.51  
 25-MAR-99:51:58 FB001075/home/ssrv026d/dsk04/dept4023/amp34723/edmmmod

292304

A