



[Click Here to Request a Large Quantity Quote](#)

Chokes

Jameco Part #	Manufacturer	Manufacturer Part #	Lead Style	Inductance (uH)	Rated Current (mA)	Tolerance	Maximum DC Resistance	Technology	Core Material	Maximum Self Resonant Frequency	Minimum Quality Factor	Price 1
<a href="#">372306</a>	Jameco Valuepro	9230-04-VP	Axial	0.22	935	10%	140 mOhm	Wirewound	Phenolic	10 MHz(Min)	33@25MHz	\$0.79
<a href="#">372314</a>	Jameco Valuepro	9230-10-VP	Axial	0.39	640	10%	300 mOhm	Wirewound	Phenolic	380 MHz(Min)	30@25MHz	\$0.79
<a href="#">372322</a>	Jameco Valuepro	9230-12-VP	Axial	0.47	590	10%	350 mOhm	Wirewound	Phenolic	340 MHz(Min)	30@25MHz	\$0.79
<a href="#">372331</a>	Jameco Valuepro	9230-14-VP	Axial	0.56	495	10%	500 mOhm	Wirewound	Phenolic	300 MHz(Min)	30@25MHz	\$0.79
<a href="#">372349</a>	Jameco Valuepro	9230-16-VP	Axial	0.68	450	10%	600 mOhm	Wirewound	Phenolic	275 MHz(Min)	28@25MHz	\$0.79
<a href="#">372453</a>	Jameco Valuepro	MCGSB-1501-1R0K	Axial	1	24	10%	70 mOhm	Wirewound	Ferrite	140 MHz(Min)	44@25MHz	\$1.95
<a href="#">2312527</a>	Vishay	B78108S1102K	Axial	1	1200	10%	160 mOhms	Bobbin Core	Ferrite	205 MHz	55@7.96MHz	\$0.35
<a href="#">372373</a>	Jameco Valuepro	9230-34-VP	Axial	3.9	350	10%	1 Ohm	Wirewound	Iron	82 MHz(Min)	45@7.9MHz	\$0.99
<a href="#">2312559</a>	EPCOS	B82144A2472K	Axial	4.7	1600	10%	160 mOhms	Bobbin Core	Ferrite	100 MHz	40@7.96MHz	\$0.69
<a href="#">372171</a>	Jameco Valuepro	78F100K-VP	Axial	10	370	0.05	720 mOhm	Bobbin Core	Ferrite	22 MHz(Min)	40@7.9MHz	\$0.45
<a href="#">2312383</a>	EPCOS	B82144-A2103-K	Axial	10	1400	10%	220 mOhm	Wirewound	Ferrite	60 MHz	60@2.52MHz	\$0.59
<a href="#">372402</a>	Jameco Valuepro	9230-52-VP	Axial	22	190	10%	3.3 Ohm	Wirewound	Iron	25 MHz(Min)	50@2.5MHz	\$0.79
<a href="#">2312471</a>	EPCOS	B82111EC22	Axial	22	3000	20%	70 mOhms	Wirewound	Ferrite	110 MHz	N/A	\$1.25
<a href="#">372411</a>	Jameco Valuepro	9230-56-VP	Axial	33	187	10%	3.4 Ohm	Wirewound	Ferrite	24 MHz(Min)	45@2.5MHz	\$0.99
<a href="#">2312503</a>	EPCOS	B78108S1393K	Axial	39	470	10%	1020 mOhms	Bobbin Core	Ferrite	8 MHz	50@2.52MHz	\$0.35
<a href="#">372429</a>	Jameco Valuepro	9230-64-VP	Axial	68	135	10%	6.7 Ohm	Wirewound	Ferrite	15 MHz(Min)	50@2.5MHz	\$0.99
<a href="#">2312519</a>	EPCOS	B78108S1683J	Axial	68	410	5%	1350 mOhms	Bobbin Core	Ferrite	6.5 MHz	40@2.52MHz	\$0.35

Jameco Part #	Manufacturer	Manufacturer Part #	Lead Style	Inductance (uH)	Rated Current (mA)	Tolerance	Maximum DC Resistance	Technology	Core Material	Maximum Self Resonant Frequency	Minimum Quality Factor	Price 1
<a href="#">208194</a>	Jameco Valuepro	CEC-101J	Axial	100	240	0.05	4.98 Ohm	Wirewound	Ferrite	5 MHz(Min)	45@2.52MHz	\$0.99
<a href="#">2312479</a>	EPCOS	B78108S1104J	Axial	100	370	5%	1700 mOhms	Bobbin Core	Ferrite	5 MHz	70@796KHz	\$0.39
<a href="#">372445</a>	Jameco Valuepro	9230-70-VP	Axial	120	97	10%	13 Ohm	Wirewound	Ferrite	12 MHz(Min)	30@790KHz	\$0.99
<a href="#">2312775</a>	Bourns	8230-72-RC	Axial	150	85	10%	15 Ohms	Wirewound	Ferrite	11 MHz	30@790KHz	\$1.75
<a href="#">2312535</a>	Vishay	B78108S1154J	Axial	150	280	5%	2800 mOhms	Bobbin Core	Ferrite	4.2 MHz	70@796KHz	\$0.35
<a href="#">372269</a>	Jameco Valuepro	78F221J-VP	Axial	220	130	0.05	5.7 Ohm	Bobbin Core	Ferrite	4 MHz(Min)	60@790KHz	\$0.39
<a href="#">2312487</a>	EPCOS	B78108S1224J	Axial	220	250	5%	3300 mOhms	Bobbin Core	Ferrite	3.7 MHz	70@796KHz	\$0.39
<a href="#">2312783</a>	Bourns	8230-80-RC	Axial	330	62	10%	28 Ohms	Wirewound	Ferrite	4 MHz	30@790KHz	\$1.75
<a href="#">2312495</a>	EPCOS	B78108S1334J	Axial	330	190	5%	6400 mOhms	Bobbin Core	Ferrite	2.7 MHz	70@796KHz	\$0.39
<a href="#">2312511</a>	EPCOS	B78108S1474J	Axial	470	170	5%	7900 mOhms	Bobbin Core	Ferrite	2.2 MHz	70@796kHz	\$0.39
<a href="#">2312391</a>	EPCOS	B82144A2684J	Axial	680	240	5%	2.8 Ohm	Wirewound	Ferrite	1.3 MHz	30@796KHz	\$0.65
<a href="#">208240</a>	Jameco Valuepro	CEC-102J	Axial	1000	160	0.1	31.3 Ohm	Wirewound	Ferrite	1.5 MHz(Min)	45@796KHz	\$0.39
<a href="#">2312551</a>	EPCOS	B82144A2105J	Axial	1000	200	5%	3800 mOhms	Bobbin Core	Ferrite	1.2 MHz	60@252KHz	\$0.59
<a href="#">642741</a>	Jameco Valuepro	VC0513-103K-UL	Axial	10000	125	10%	26.4 Ohm	Bobbin Core	Ferrite	N/A	N/A	\$0.89
<a href="#">2279935</a>	Jameco Valuepro	VC1019-103K-UL-1KV	Axial	10000	266	10%	7.3 Ohm	Wirewound	Ferrite	N/A	N/A	\$0.99
<a href="#">642927</a>	Jameco Valuepro	GSPCU1020-103K08	Axial	10000	350	10%	7.3 Ohm	Bobbin Core	Ferrite	N/A	N/A	\$1.29
<a href="#">2233967</a>	Jameco Valuepro	VC1019-503K-UL	Axial	50000	100	10%	38.0 Ohm	Wirewound	Ferrite	N/A	N/A	\$1.29
<a href="#">2233959</a>	Jameco Valuepro	VC1019-104K-UL-CID	Axial	100000	65	0.1	77.3 Ohm	Wirewound	Ferrite	N/A	N/A	\$1.29
<a href="#">2314223</a>	Murata	A119ANS-1031Z	Radial	6.8		10%	N/A	N/A	N/A	7.96 MHz	80@7.96MHz	\$1.95
<a href="#">2314231</a>	Murata	A119ANS-1038Z	Radial	27		10%	N/A	N/A	N/A	2.52 MHz	80@2.52MHz	\$1.95
<a href="#">2312567</a>	Pulse Electronics	PE-53113	Radial	150	2000	20%	100 mOhms	Toroid	Leaded	N/A	N/A	\$2.49
<a href="#">2312359</a>	Bourns	RLB9012-102KL	Radial	1000	510	10%	2.9 Ohm	Wirewound	Ferrite	1.3 MHz	20@252KHz	\$0.55
<a href="#">2287095</a>	Yageo Corporation	SL0608T-472K-B-N	Radial	4700	52	10%	15 Ohm	Bobbin Core	Ferrite	N/A	N/A	\$0.59

Jameco Part #	Manufacturer	Manufacturer Part #	Lead Style	Inductance (uH)	Rated Current (mA)	Tolerance	Maximum DC Resistance	Technology	Core Material	Maximum Self Resonant Frequency	Minimum Quality Factor	Price 1
<a href="#">2320391</a>	Würth	744227S	SMD	51	1000	30%	160 mOhms	Wirewound	Ferrite	1 KHz	1@30MHz	\$2.49